



RJ-45-Connector | 4-pole, IP20, for field assembly

Technical data	
Protection level	IP20
Mating face	RJ45 according to IEC 60603-7
Mating cycles	min. 750
Temperature range	-40 °C ...+70 °C
Cable diameter	6,5 mm – 6,9 mm
Wire insulation	max. 1,6 mm Ø
Wire diameter	AWG22/1 to AWG 23/1; AWG22/7 to AWG 24/7

Ordering information	Description
ZS1090-0003	RJ-45-Connector, 4-pole, IP20, for field assembly
Packaging unit	10 pieces