



**RJ-45-Connector | 8-pole, IP20, field assembly, suitable for Gigabit-Ethernet**

Technical data	
Protection level	IP20
Mating face	RJ45 according IEC 60603-7
Mating cycles	min. 750 according IEC 60603-7
Temperature range	-40 °C ...+70 °C
Cable diameter	5,5 mm – 8,5 mm
Wire insulation	max. 1,6 mm Ø
Wire gauge data	AWG22 - AWG26

Ordering information	Description
ZS1090-0005	RJ-45-Connector, 8-pole, IP20, field assembly, adapted for Gigabit-Ethernet
Packaging unit	10 pieces