



ZS2020-4308 | Power distribution box



Top view



I/O connection

Connector assignment

i **Product status:** regular delivery

power distribution box, 8 x M8, 4-pin, 1 x 7/8" 5-pin

Product information

Technical data

Technical data	ZS2020-4308
Number of outputs	8
Power supply connection	7/8" plug, 5-pin
Outgoing circuits	M8, screw type, 4-pin
Current load	$I_{\Sigma} = 4 \text{ A}$ per U _s and U _p
Dimensions (W x H x D)	30 mm x 126 mm x 31 mm
Operating temperature	-25...+60 °C
Storage temperature	-40...+85 °C
Protection rating	IP65/66/67 (according to EN 60529)
Installation position	variable
Nominal voltage	24 V DC
Material	PA6 (polyamide)

Ordering information

Ordering information

ZS2020-2810	7/8", plug, plastic, screw type, straight, male, 5-pin, 0.5...1.5 mm ² , Ø 6...12 mm
ZS2020-2820	7/8", socket, plastic, screw type, straight, female, 5-pin, 0.5...1.5 mm ² , Ø6...12 mm
ZS2020-2830	Plug field assembly, Power, IP67, 7/8", angled, male, 5-pin
ZS2020-2840	Socket field assembly, Power, IP67, 7/8", angled, female, 5-pin
ZS2020-4304	power distribution box, 4 x M8, 4-pin, 1 x 7/8" 5-pin
ZS2020-4308	power distribution box, 8 x M8, 4-pin, 1 x 7/8" 5-pin