

BECKHOFF New Automation Technology

4:3 – 5:4 ratio Control Panels and Panel PCs



The comprehensive display portfolio – from classic 4:3/5:4 to modern widescreen.

Beckhoff Automation is known for a comprehensive range of industrial displays that serve as reliable HMI hardware and powerful, all-in-one machine controllers. While Beckhoff has introduced an exciting range of modern screen formats, including widescreen and panels that can be installed in landscape or portrait orientation, we haven't forgotten about the large number of applications that require displays in traditional 4:3/5:4 format. So while other vendors are making 4:3/5:4 panels and HMIs obsolete, Beckhoff continues to provide them as part of the company's overall Control Panel and Panel PC portfolio. In fact, we have continued to integrate the latest display technologies across the board, including multi-touch screen technologies that can be applied across screen formats, including in 4:3/5:4 versions.

Multi-touch Control Panels and Panel PCs



12-inch 15-inch 19-inch

- front side IP 65
- for control cabinet installation



12-inch 15-inch 19-inch

- all sides IP 65
- for mounting arm installation

Single-touch Control Panels and Panel PCs



5.7 6.5-inch 12-inch 15-inch 19-inch

- front side IP 65
- for control cabinet installation

The Beckhoff Control Panel and Panel PC product families offer easy installation in control cabinets, pendants or on mounting arms and poles for machines, manufacturing facilities and in buildings. High quality materials are used for the panel housings, including milled aluminum, steel and stainless steel. These can be applied in all manner of industries and meet application-specific requirements, from metalworking, plastics, packaging, food and beverage, building automation and much more. All Beckhoff Control Panels and Panel PCs can be completely customized according to the customer's brand identity. This can include a company logo, corporate colors, specific panel layouts to factor in buttons, switches, keys, joysticks and much more.

Beckhoff Control Panels

These operator interface and display units are independent and separate from the controller. In this case the PC-based controller is located in the control cabinet. This control concept, which has been thoroughly implemented using the Beckhoff Control Panel, allows the user a great deal of freedom.

The CP6xxx and CP7xxx series Control Panels are designed for use as human-machine interfaces (HMIs). Interface and display elements create an independent unit, separate from the control level. Beckhoff Control Panels feature robust, yet elegant designs, with large screens available to the user, but in a low hardware depth. The PC-based controller is protected in the control cabinet, yet remains easily accessible.

Multi-touch Control Panels from Beckhoff are conceived both for control cabinet installation and for mounting arm installation. The CP29xx built-in Panel series is implemented with IP 65 protection at the front and IP 20 at the rear. The CP39xx Control Panels for mounting arm installation feature all-round IP 65 protection. The panels in the CP29xx-0000 and CP39xx-0000 ranges with DVI/USB Extended interface can be operated up to 50 m away from the Industrial PC. By combining CP-Link 4 – The One Cable Display Link – with CP29xx-0010 and CP39xx-0010 Control Panels, the distance between PC-based controller and the operator interface panels can be increased to 100 m.

Beckhoff Panel PCs

All Beckhoff Panel PCs are equipped with powerful processors from Intel® Atom™ to Core™ i7. The series provides the appropriate Panel PC for every application, according to the available installation space. All housings are optimized in terms of space utilization and easy accessibility of all connectors and components.

The Panel PCs of the CP2xxx and CP3xxx series offer multi-touch functionality in 4:3/5:4 and wide-screen display sizes (optionally also in portrait format). The Panel PCs of the CP6xxx and CP7xxx series can be equipped with single-touch functionality, touch pad or different front laminates.



Beckhoff offers the following display sizes:


Conventional display sizes

- 5.7-inch, resolution 640 x 480 (4:3)
- 6.5-inch, resolution 640 x 480 (4:3)
- 12-inch, resolution 800 x 600 (4:3)
- 15-inch, resolution 1024 x 768 (4:3)
- 19-inch, resolution 1280 x 1024 (5:4)

Wide screen (16:9)

- 7-inch, resolution 800 x 480
- 11.6-inch, resolution 1366 x 768
- 15.6-inch, resolution 1366 x 768
- 18.5-inch, resolution 1366 x 768
- 21.5-inch, full HD resolution 1920 x 1080
- 24-inch, full HD resolution 1920 x 1080

The right Industrial PC for every application





CP2xxx |
Multi-touch
built-in Panel PC

CP79xx |
Stainless steel
panel

CP6xxx |
Control Panel

C52xx |
19-inch slide-in
Industrial PC

C65xx |
Control cabinet
Industrial PC

Beckhoff Industrial PCs satisfy industry's demands:

- the right Industrial PC for every controller
- highest performance PCs with Intel® Celeron® up to Intel® Core™ i7 processors
- PCs with low power consumption with Intel® Mobile processors
- open standards following the norm ATX
- components carefully tested to ensure appropriateness for industrial applications
- appealing industrial design housings
- easy access to PC components
- Individual housing construction allows optimum adaptation to controller requirements.
- integration of electromechanical buttons, switches, scanners, handwheels and other components in the Control Panel
- designed for machine-oriented use
- long-term availability of components



C6670 |
Control cabinet
industrial server

► www.beckhoff.com/IPC

Multi-touch Panel PCs in 4:3/5:4



| Multi-touch built-in Panel PCs, front side IP 65 | | | | |
|--|--|-----------|------------|-------------|
| | Display | 12-inch | 15-inch | 19-inch |
| | Resolution | 800 x 600 | 1024 x 768 | 1280 x 1024 |
| | Format | 4:3 | 4:3 | 5:4 |
| CP22xx-0000/-0010 – up to Core™ i3/i5/i7 | multi-finger touch screen | CP2212 | CP2215 | CP2219 |
| CP26xx-0000 – ARM Cortex™-A8 | dual-finger touch screen | CP2612 | CP2615 | CP2619 |
| CP27xx-0000/-0010 – up to Atom™ | multi-finger touch screen, only horizontal | CP2712 | CP2715 | CP2719 |

| Multi-touch Panel PCs, all sides IP 65 | | | | |
|--|--|-----------|------------|-------------|
| | Display | 12-inch | 15-inch | 19-inch |
| | Resolution | 800 x 600 | 1024 x 768 | 1280 x 1024 |
| | Format | 4:3 | 4:3 | 5:4 |
| CP32xx-0000/-0010 – up to Core™ i3/i5/i7 | multi-finger touch screen, only horizontal | CP3212 | CP3215 | CP3219 |
| CP37xx-0010 – up to Atom™ | multi-finger touch screen, only horizontal | CP3712 | CP3715 | CP3719 |

For further information on the complete range of Control Panel and Panel PC ratios, incl. widescreen formats, please visit

► www.beckhoff.com/multi-touch

Multi-touch Control Panels in 4:3/5:4



CP29xx



CP39xx

Multi-touch built-in Control Panels, front side IP 65

| | Display | 12-inch | 15-inch | 19-inch |
|--|---------------------------|-------------|-------------|-------------|
| | Resolution | 800 x 600 | 1024 x 768 | 1280 x 1024 |
| | Format | 4:3 | 4:3 | 5:4 |
| CP29xx-0000 – DVI/USB Extended interface | multi-finger touch screen | CP2912-0000 | CP2915-0000 | CP2919-0000 |
| CP29xx-0010 – CP-Link 4 | multi-finger touch screen | CP2912-0010 | CP2915-0010 | CP2919-0010 |

Multi-touch Control Panels, all sides IP 65

| | Display | 12-inch | 15-inch | 19-inch |
|--|---------------------------|-------------|-------------|-------------|
| | Resolution | 800 x 600 | 1024 x 768 | 1280 x 1024 |
| | Format | 4:3 | 4:3 | 5:4 |
| CP39xx-0000 – DVI/USB Extended interface | multi-finger touch screen | CP3912-0000 | CP3915-0000 | CP3919-0000 |
| CP39xx-0010 – CP-Link 4 | multi-finger touch screen | CP3912-0010 | CP3915-0010 | CP3919-0010 |

For further information on CP-Link 4 ► www.beckhoff.com/CP-Link4

For further information on the complete range of Control Panel and Panel PC ratios, incl. widescreen formats, please visit
► www.beckhoff.com/multi-touch

Single-touch Panels in 4:3/5:4



Single-touch built-in Panel PCs, front side IP 65

| | Display | 5.7-inch | 6.5-inch | 12-inch | 15-inch | 19-inch |
|--|----------------|-----------|-----------|-----------|------------|-------------|
| | Resolution | 640 x 480 | 640 x 480 | 800 x 600 | 1024 x 768 | 1280 x 1024 |
| | Format | 4:3 | 4:3 | 4:3 | 4:3 | 5:4 |
| CP62xx – 3½-inch motherboard – up to Core™ i3/i5/i7 | without keys | | | CP6201 | CP6202 | CP6203 |
| | function keys | | | CP6211 | CP6212 | CP6213 |
| | numerical | | | CP6221 | CP6222 | CP6223 |
| | alphanumerical | | | CP6231 | CP6232/42 | CP6233 |
| CP65xx – ATX motherboard – up to Core™ i3/i5/i7 – 7 slots free | without keys | | | CP6501 | CP6502 | CP6503 |
| | function keys | | | CP6511 | CP6512 | CP6513 |
| | numerical | | | CP6521 | CP6522 | CP6523 |
| | alphanumerical | | | CP6531 | CP6532/42 | CP6533 |
| CP66xx – 3½-inch motherboard – ARM Cortex™-A8 | without keys | CP6607 | CP6609 | CP6601 | CP6602 | CP6603 |
| | function keys | | CP6619 | CP6611 | CP6612 | CP6613 |
| | numerical | | CP6629 | CP6621 | CP6622 | CP6623 |
| | alphanumerical | | | CP6631 | CP6632 | CP6633 |
| CP67xx – 3½-inch motherboard – Celeron™ ULV or Atom™ | without keys | CP6707 | <i>i</i> | CP6701 | CP6702 | CP6703 |
| | function keys | | | CP6711 | CP6712 | CP6713 |
| | numerical | | | CP6721 | CP6722 | CP6723 |
| | alphanumerical | | | CP6731 | CP6732/42 | CP6733 |
| C36xx – ATX motherboard – up to Core™ i3/i5/i7 – 7 slots free | without keys | | | C3620 | C3640 | |

Single-touch Panel PCs, all sides IP 65

| | Display | 5.7-inch | 6.5-inch | 12-inch | 15-inch | 19-inch |
|--|----------------|-----------|-----------|-----------|------------|-------------|
| | Resolution | 640 x 480 | 640 x 480 | 800 x 600 | 1024 x 768 | 1280 x 1024 |
| | Format | 4:3 | 4:3 | 4:3 | 4:3 | 5:4 |
| CP72xx – 3½-inch motherboard – up to Core™ i3/i5/i7 | without keys | | | CP7201 | CP7202 | CP7203 |
| | function keys | | | CP7211 | CP7212 | CP7213 |
| | numerical | | | CP7221 | CP7222 | CP7223 |
| | alphanumerical | | | CP7231 | CP7232/42 | CP7233 |
| CP77xx – CP motherboard – Celeron® ULV | without keys | | | CP7701 | CP7702 | CP7703 |
| | function keys | | | CP7711 | CP7712 | CP7713 |
| | numerical | | | CP7721 | CP7722 | CP7723 |
| | alphanumerical | | | CP7731 | CP7732 | CP7733 |



Single-touch built-in Control Panels, front side IP 65

| | Display | 5.7-inch | 6.5-inch | 12-inch | 15-inch | 19-inch |
|---|----------------|-----------|-----------|-----------|------------------|-------------|
| | Resolution | 640 x 480 | 640 x 480 | 800 x 600 | 1024 x 768 | 1280 x 1024 |
| | Format | 4:3 | 4:3 | 4:3 | 4:3 | 5:4 |
| CP69xx – DVI/USB Extended interface | without keys | CP6907 | CP6909 | CP6901 | CP6902 | CP6903 |
| | function keys | | CP6919 | CP6911 | CP6912 | CP6913 |
| | numerical | | CP6929 | CP6921 | CP6922 | CP6923 |
| | alphanumerical | | | CP6931 | CP6932 CP6942 | CP6933 |

Single-touch Control Panels, all sides IP 65

| | Display | 5.7-inch | 6.5-inch | 12-inch | 15-inch | 19-inch |
|---|----------------|-----------|-----------|-----------|------------------|-------------|
| | Resolution | 640 x 480 | 640 x 480 | 800 x 600 | 1024 x 768 | 1280 x 1024 |
| | Format | 4:3 | 4:3 | 4:3 | 4:3 | 5:4 |
| CP79xx – DVI/USB Extended interface | without keys | | CP7909 | CP7901 | CP7902 | CP7903 |
| | function keys | | CP7919 | CP7911 | CP7912 | CP7913 |
| | numerical | | CP7929 | CP7921 | CP7922 | CP7923 |
| | alphanumerical | | | CP7931 | CP7932 CP7942 | CP7933 |

Single-touch Control Panels in stainless steel housing, all sides IP 65

| | Display | 5.7-inch | 6.5-inch | 12-inch | 15-inch | 19-inch |
|---|--------------|-----------|-----------|-------------|-------------|-------------|
| | Resolution | 640 x 480 | 640 x 480 | 800 x 600 | 1024 x 768 | 1280 x 1024 |
| | Format | 4:3 | 4:3 | 4:3 | 4:3 | 5:4 |
| CP79xx – DVI/USB Extended interface | without keys | | | CP7901-14xx | CP7902-14xx | CP7903-14xx |

For further information on the complete range of Control Panel and Panel PC ratios please visit
 ► www.beckhoff.com/single-touch

Headquarters

Beckhoff Automation GmbH & Co. KG

Huelshorstweg 20
33415 Verl
Germany
Phone: +49 5246 963-0
info@beckhoff.com
www.beckhoff.com

Products online

At www.beckhoff.com you can get detailed information on the range of products from Beckhoff. Animations, videos and interactive online presentations supplement the large variety of information.

► www.beckhoff.com



Print media online

The Beckhoff catalogs and flyers are available for download on the Internet. Printed copies are available on request. Please use our online order form to specify your requirements.

► www.beckhoff.com/media

► www.pc-control.net



Main catalog



PC control magazine (additionally as App)



Beckhoff®, TwinCAT®, EtherCAT®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC® and XTS® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 07/2016

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.