



ZS1031-2610 | Plug T splitter for PROFIBUS, Modbus, RS485, IP 67, without 5 V on the plug, shielded

M12, T splitter, straight, male+female, 5-pin, B-coded

Electrical data	
Rated voltage	60 V (according to IEC 61076-2-101)
Rated current	0.4 A at 40°C
Shielding	yes
Insulation resistance	≥ 100 MΩ (according to IEC 60512)
Insulation group	II
Mechanical data	
Installation size	M12
Connector type	T splitter
Configuration	straight
Contact type	male+female
Number of positions (face)	5-pin
Coding	B-coded
Body material	TPU
Environmental data	
Ambient temperature (operation)	-30...+90 °C, -22...+194 °F
Protection class	IP 67 in screwed condition (according to IEC 60529)
Pollution level	3

