


ZS1090-0002 | RJ45 plug field assembly, IP 67

RJ45, plug, straight, male, 8-pin

Electrical data	
Mechanical data	
Installation size	RJ45
Connector type	plug
Configuration	straight
Contact type	male
Number of positions (face)	8-pin
Weight per piece	0.015 kg (0.0101 lb)
Body material	PA
Seal	NBR
Max. wire cross section	AWG24 ... AWG26 (0.25 mm ² ... 0.14 mm ²)
Max. cable outer diameter	4.0 - 5.4 mm
Environmental data	
Ambient temperature (operation)	-5...+60 °C, +23...+140 °F
Protection class	IP65/IP 67 (according to EN 60529)

Dimensions



A1	53.50 mm
----	----------

Notes

- Illustrations similar

Ordering information	
ZS1090-0002	plug, field assembly, RJ45, IP 67, straight, male, 8-pin, 0.14...0.34 mm ² , Ø 4...5.4 mm

Beckhoff®, TwinCAT®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2021

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.