

# ZS5000-0020 | blanking plug, M12, plastic, black, IP65/67, for M12 socket



M12, protection cap, straight



Mechanical data	
Accessories type	Protection cap
Installation size	M12
Connector type	protection cap
Configuration	straight
Recommended torque, nut	0.6 Nm
Way of locking	screw
Weight per piece	0.088 kg (0.1940 lb)
Body color	black
Body material	PA GF, UL94 V-0
Environmental data	
Special features	packaging unit = 50 pcs.
Ambient temperature (operation)	-30...+120 °C, -22...+248 °F
Protection rating	IP65/67 in screwed condition (according to IEC 60529)

Dimensions	
------------	--

---

## Notes

- Illustrations similar

---

### Ordering information

ZS5000-0020

blanking plug, plastic (IP67), for M12 socket, packaging unit = 50 pieces

---

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 09/2023

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.