


- 1 | yellow
- 2 | orange
- 3 | white
- 6 | blue

RJ45, 8-pin



- 1 | Tx+
- 2 | Rx+
- 3 | Tx-
- 4 | Rx-

Socket M12, 5-pin

### EtherCAT cable | M12 flange, straight, d-coded, 4-pin – RJ 45 plug, straight

Electrical data	ZK1090-6292-0xxx
Rated voltage	160 V (according to IEC 61076-2-101)
Rated current	4 A at 40 °C (according to IEC 61076-2-101)
Insulation resistance	≥ 10 GΩ (according to IEC 60512-2)
DC resistance	max. 58 Ω/km at 20 °C
Nominal impedance	1...100 MHz, (100 ±15) Ω
Shielding	aluminium-clad foil, braiding of tinned copper wires
Electrical parameters	according to EN 50288-2-1

Mechanical data	
Protection class	IP 67 in screwed condition (according to IEC 60529)
Ambient temperature	-30 °C...+80 °C (according to IEC 60644-1)
Insertion cycles	≤ 100 (according to IEC 60512-9a)
Contamination level	3/2 (according to IEC 60664-1)

Mechanical properties cable	
Temperature range (cable)	-40 °C...+70 °C
Cable outside diameter	6.50 ±0.20 mm
Drag chain suitable	yes
Bending radius	200 mm
Number of cycles	min. 3 million
Parameter	max. velocity 4 m/s, acceleration max. 4 m/sec <sup>2</sup>
Approbations	UL Style 119100 VOL.1 SEC.13 Page 1
Material properties	RoHS-compliant, halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1
Wire pair 1	7 x 0.25, WS/GE/BU/OR

Materials	
Contact material	CuZn
Contact surface	Ni, Au gal.
Contact carrier/body	TPU GF, UL 94/TPU, UL 94
Coupling screw/nut	CuZn, Ni
Seal	FPM
Cable	TPU, UL, 4-wire around filler, 4 x AWG22, green

Ordering information	Cable length
ZK1090-6292-0005	0.5 m
ZK1090-6292-0020	2.0 m
ZK1090-6292-0050	5.0 m
ZK1090-6292-0100	10.0 m