



**ZB8800 | Torque wrench for M8 cables with knurl, incl. ratchet, adjustable 0.5 ... 1.7 Nm**

Mechanical Data	
<b>Grip</b>	Comfortable soft grip ergonomic handle Easy View Scale in Newton Meter Increments Secured torque setting, Required adjustment tool included Long life internal mechanisms, cycle tested for durability "Click sound" when torque is reached
<b>Application</b>	Precise adjustment at a given torque, in combination with different blades for different screws
<b>Precision</b>	±6% acc. to standards
<b>Torque</b>	0.5 ... 1.7 Nm, (suggested values: M8 = 0.4 Nm (when using the torque control screwdriver ZB8800 is also a max. torque of 0.5 Nm permissible!), M12 = 0.6 Nm)
<b>Adjustment</b>	Adjustable by direct reading Newton meter scales
<b>Standards</b>	EN ISO 6789, BS EN 26789, ASME B107.14M
Order information	
<b>ZB8800</b>	Torque wrench for M8 cables with knurl, incl. ratchet
<b>ZB8800-0001</b>	M12 ratchet for ZB8800
<b>ZB8800-0002</b>	M8 ratchet (field assembly) for ZB8800

**ZB8800-0001**



**ZB8800-0002**

