



ZB8801-0000 | Torque wrench for hexagonal plugs, adjustable, adjustable 0.4 ... 1.0 Nm

Mechanical Data	
Grip	Comfortable soft grip ergonomic handle Easy View Scale in Newton Meter Increments Secured torque setting, Required adjustment tool included Long life internal mechanisms, cycle tested for durability "Click sound" when torque is reached
Application	Precise adjustment at a given torque, in combination with different blades for different screws
Precision	±6% acc. to standards
Torque	0.4 ... 1.0 Nm, (suggested values M8 = 0.4 Nm, M12 = 0.6 Nm)
Adjustment	Adjustable by direct reading Newton meter scales
Standards	EN ISO 6789, BS EN 26789, ASME B107.14M
Mechanical data key	
Material	Robust, glass fiber reinforced plastic Hexagon stainless steel cable key Chromium -Molybdenum steel shaft

Note: The hexagonkey can be used on all EtherCAT-/Power and sensor cordsets with integrated hexagon nut. For cordsets with knurled screw the tool ZB8800 is recommended!

Order information	
ZB8801-0000	Torque wrench for hexagonal plugs, adjustable
ZB8801-0001	Torque cable key, M8/wrench size 9, for ZB8801-0000
ZB8801-0002	Torque cable key, M12/wrench size 13, for ZB8801-0000
ZB8801-0003	Torque cable key, M12F/wrench size 13, for ZB8801-0000

ZB8801-0001



ZB8801-0002



ZB8801-0003

