

# ZS2030-4812 | M12, T splitter, 1 x M12, plug, straight, male, L-coded – 2 x M12, socket, straight, female, L-coded, pin assignment 1:1



M12, T splitter, male+female, 5-pin (4+FE), L-coded



Electrical data	
Rated voltage	63 V DC
Rated current	16 A at 40 °C (according to IEC 60512-3), 12 A at 25 °C (according to UL)
Shielding	no
Insulation resistance	≥ 100 MΩ
Mechanical data	
Installation size	M12
Connector type	T splitter
Contact type	male+female
Number of positions (face)	5-pin (4+FE)
Coding	L-coded
Recommended torque, nut	0.6 Nm
Mating cycles	≥ 100 (according to IEC 60512-9a)
Way of locking	screw
Body color	black
Body material	TPU



**Ordering information**

ZS2030-4812	M12, T splitter, 1 x M12 (plug) – 2 x M12 (socket), pin assignment 1:1, straight, male+female, 5-pin, unshielded, L-coded
-------------	---

**Accessories**

ZB8801-0000	torque wrench for hexagonal plugs, adjustable
ZB8801-0002	torque cable key, M12/wrench size 13, for ZB8801-0000

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 10/2022

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.