



Sensor cable | **Sensor cable, 4 x 0.25 mm<sup>2</sup>, PVC**

<b>Electrical data</b>	<b>ZB9043</b>
Operating voltage	≤ 300 V
Test voltage	≥ 3.000 V
Conductor resistance	Max. 58 Ω/km (20 °C)
Surface resistance	≥ 10 <sup>13</sup> Ω cm (20 °C)
<b>Mechanical data</b>	
Temperature	-25 °C...+85 °C
<b>Mechanical properties cable</b>	
Conductor	4-wire, 32 x 0.10 mm
Isolation	PVC 1.32 ± 0.02 mm
Sheath	4.70 ± 0.15 mm Ø
<b>Materials</b>	
Material properties	Flame retardant DIN EN60332-2-2, RoHS-compliant, PVC
Cable	Grey, 4 x 0.25 mm <sup>2</sup> , LiYY
<b>Ordering information</b>	
ZB9043	Cable sold by meter