

# ZK1090-3131-6xxx | EtherCAT cable, PUR, 1 x 4 x AWG22, capable of torsion



M8, plug, straight, male, 4-pin, A-coded – M8, plug, straight, male, 4-pin, A-coded



## Plugs

Electrical data	Head A	Head B
Rated voltage	63 V (according to IEC 61076-2-111)	63 V (according to IEC 61076-2-111)
Rated current	4 A at 40°C (according to IEC 61076-2-104)	4 A at 40°C (according to IEC 61076-2-104)
Shielding	yes	yes
Insulation resistance	≥ 100 GΩ (according to IEC 60512)	≥ 100 GΩ (according to IEC 60512)
Mechanical data		
Installation size	M8	M8
Connector type	plug	plug
Configuration	straight	straight
Contact type	male	male
Number of positions (face)	4-pin	4-pin
Coding	A-coded	A-coded
Recommended torque, nut	0.4 Nm	0.4 Nm
Mating cycles	≥ 100	≥ 100

Way of locking	screw	screw
Weight per piece	0.028 kg (0.0617 lb)	0.028 kg (0.0617 lb)
Body color	black	black
Body material	TPU, UL94	TPU, UL94
Coupling nut material	GD-Zn, Ni	GD-Zn, Ni
Seal	FPM	FPM
Contact carrier color	green	green
Contact carrier material	PA 6, UL 94 V0	PA 6, UL 94 V0
Contact plating	Ni, Au gal.	Ni, Au gal.
Contact material	CuZn	CuZn
<b>Environmental data</b>		
Special features	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1
RoHS compliant	yes	yes
Ambient temperature (operation)	-30...+70°C, -22...+158°F	-30...+70°C, -22...+158°F
Protection rating	IP65/67 in screwed condition (according to IEC 60529)	IP65/67 in screwed condition (according to IEC 60529)
Pollution level	3/2 (according to IEC 60664-1)	3/2 (according to IEC 60664-1)

## Cable


<b>Electrical data</b>		
Rated voltage	600 V	
Insulation resistance	≥ 5GΩ * km	
Mutual capacitance	48 nF/km	
Characteristic impedance (Ethernet)	100 Ω ±15 Ω	
Loop resistance (Ethernet)	≤ 115 Ω/km	
Signal running time (Ethernet)	5.3 ns/m	
Electrical parameters (Ethernet)	based on Cat.5	
Test voltage	1500 V, 50 Hz, 1 min.	
<b>Mechanical data</b>		
Cable structure (Ethernet)	star quad	
Conductor construction (Ethernet)	19-strand	
Cross-section (Ethernet)	1 x 4 x 0.34 mm <sup>2</sup> (AWG22)	
Outer cable diameter	6.6 mm ± 0.2mm (0.259" ± 0.0079")	
Min. bending radius, moved	10 x outer cable diameter	
Min. bending radius, fixed installation	5 x outer cable diameter	

Conductor material (Ethernet)	copper, tinned
Shielding	two layers of conductive wrapping and braiding of special wires
Optical covering factor of shielding (Ethernet)	≥ 85 %
Use	suitable for torsion/robotic application
Max. acceleration	20 m/s <sup>2</sup>
Max. speed	4 m/s
Max. travel distance	5 m
Max. number of cycles	1 million
Jacket color	green
Material jacket	PUR (polyurethane)
Material jacket, further characteristics of	halogen-free, flame-retardant, matt and low adhesion
Wire color code	yellow, orange, white, blue
Wire insulation material	PO (Polyolefine)
Printing on the jacket	XXX Beckhoff Automation GmbH & Co. KG-Germany-ZB9021 EtherCAT Cat5e Torsion AWG22/19 E170315 cRUus> AWM21209 AWM I/II A/B 90°C 600V MM/YY CE
Printing color	black
Torsion angle in °/m	max. ± 180°/m
Torsion speed	36 cycle/min.
Number of torsion cycles	5 million
Load weight	20 N
Claimed torsion length	1 m
<b>Environmental data</b>	
Operation temperature range, moved	-30...+90°C, -22...+194°F
Operation temperature range, fixed installation	-40...+90°C, -40...+194°F
Oil resistance	according to DIN EN 60811-404 (7x24 h/90 °C)
Flame-retardant	VW-1 Flame Test UL 1581 section 1080 and IEC 60332-1-2
Halogen-free	according to IEC 60754 or DIN VDE 0472 part 815
UL	yes, UL E-file number: E170315


<b>Attenuation</b>	
Max. insertion loss	
Frequency [MHz]	1      4      10      16      20      31.25      62.5      100
[db/100 m]	-      4.9      7.8      9.9      11.1      14.1      62.5      26.4
[db/100 ft]	-      1.5      2.4      3      3.4      4.3      19.1      8
Min. near-end crosstalk attenuation	
Frequency [MHz]	1      4      10      16      20      31.25      62.5      100

[db/100 m]	-	56.3	50.3	47.2	45.8	42.9	38.4	35.3
[db/100 ft]	-	17.2	15.3	14.4	14	13.1	11.7	10.8

### Contact assembly



### Dimensions



A1	41.00 mm
A2	Ø 10.1 mm
B1	41.00 mm
B2	Ø 10.1 mm

## Notes

- Depending on the cable length (L), the following length tolerances apply:  
0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: + 40 mm | ≥ 4.0 m: + 1%
- Illustrations similar
- Further cable length on request.

### CE, UL

CE	yes
UL	yes, UL E-file number: E480185

### Ordering information

Ordering information	Length
ZK1090-3131-6001	0.13 m
ZK1090-3131-6003	0.30 m

ZK1090-3131-6005	0.50 m
ZK1090-3131-6020	2.00 m
ZK1090-3131-6030	3.00 m
ZK1090-3131-6050	5.00 m
ZK1090-3131-6075	7.50 m
ZK1090-3131-6100	10.00 m
ZK1090-3131-6120	12.00 m
ZK1090-3131-6200	20.00 m
ZK1090-3131-6400	40.00 m

### Accessories

ZB8801-0000	torque wrench for hexagonal plugs, adjustable
ZB8801-0001	torque cable key, M8/wrench size 9, for ZB8801-0000
ZB8803-0001	Flange/Panel feed-through for M8 pre-assembled, for fixing the connector, plastic



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2024

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.