



ZK2002-2200-0xxx | Sensor cable, PUR, 3 x 0.25 mm², drag-chain suitable

M8, socket, straight, female, 3-pin, A-coded – open end, 3-wire

Plugs


Electrical data	Head A	Head B
Rated voltage	60 V (according to IEC 61076-2-104)	-
Rated current	3 A at 40 °C (according to IEC 61076-2-104)	-
Rated current (signal/24V)	4 A at 40 °C (acc.to IEC 61076-2-104)	-
Shielding	no	-
Insulation resistance	≥ 10 GΩ (according to IEC 60512-2)	-
Mechanical data		
Installation size	M8	open end
Connector type	socket	-
Configuration	straight	-
Contact type	female	-
Number of positions (face)	3-pin	3-wire
Coding	A-coded	-
LED	with LED	-
Wire termination	crimp connection	-
Recommended torque, nut	0.4 Nm	-
Mating cycles	≥ 100 (according to IEC 60512-9a)	-
Way of locking	screw	-
Weight per piece	0.028 kg (0.0617 lb)	-
Body colour	transparent	-
Body material	TPU, UL94	-
Coupling nut material	CuZn, Ni	-
Seal	FPM	-
Contact carrier colour	red	-
Contact carrier material	TPU GF, UL 94	-
Contact plating	Ni, Au gal.	-
Contact material	CuZn	-
Environmental data		

Special features	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1	-
RoHS compliant	yes	-
Ambient temperature (operation)	-30...+80 °C, -22...+176 °F	-
Protection class	IP 67 in screwed condition (according to IEC 60529)	-
Pollution level	3/2 (according to IEC 60664-1)	-


Cable

Electrical data	
Rated voltage	≤ 300 V
Insulation resistance	≥ 10 GΩ (according to IEC 60512-2)
Wire resistance (signal/24V)	≤ 58.0 Ω/km (20 °C)
Test voltage	≥ 3000 V
Mechanical data	
Conductor construction (signal/24V)	32 x 0.10 mm
Cross section	3 x 0.25 mm ² (AWG24)
Min. bending radius, moved	6 x outer cable diameter
Weight	28 kg/km (18.8 lb/1000 ft)
Outer cable diameter	4.4 mm ± 0.15 mm (0.173" ± 0.0059")
Shielding	no
Use	drag-chain suitable
Max. acceleration	10 m/s ²
Max. speed	5 m/s
Max. number of cycles	10 million at max. 20 m travel distance, 2 million at max. 100 m travel distance
Jacket colour	black
Material jacket	PUR (polyurethane)
Wire colour code	brown, blue, black
Wire insulation material	PP (polypropylene)
Printing colour	white
Environmental data	
Operation temperature range, moved	-25...+80 °C, -13...+176 °F
Oil resistance	Oil and greases resistant
Flame-retardant	according to cULus 20549
Halogen-free	DIN VDE 0472 part 815
Approvals	UL Listed: FILE E480185

Contact assembly



Dimensions



A1	33.60 mm
----	----------

Notes

- Depending on the cable length (L), the following length tolerances apply:
 0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: $+ 40$ mm | ≥ 4.0 m: $+ 1$ %
- Illustrations similar
- Further cable length on request. The last three digits of the ordering information is the cable length in decimeters, e.g. ZKxxxx-xxxx-x020 = cable length 2.00 m

Ordering information	Length
ZK2002-2200-0010	1.00 m
ZK2002-2200-0030	3.00 m
ZK2002-2200-0050	5.00 m
ZK2002-2200-0100	10.00 m
ZK2002-2200-0150	15.00 m
ZK2002-2200-0200	20.00 m

Accessories	
ZB8801-0000	torque wrench for hexagonal plugs, adjustable
ZB8801-0001	torque cable key, M8/wrench size 9, for ZB8801-0000

Beckhoff®, TwinCAT®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2021

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.