


ZK2002-6134-0xxx | Sensor cable, PUR, 4 x 0.34 mm², drag-chain suitable



M12, plug, straight, male, 4-pin, A-coded – M8, socket, angled, female, 4-pin, A-coded



Plugs


Electrical data	Head A	Head B
Rated voltage	250 V (according to IEC 61076-2-101)	30 V (according to IEC 61076-2-104)
Rated current	4 A at 40 °C (according to IEC 61076-2-101)	4 A at 40 °C (leaning on IEC 61076-2-104)
Rated impulse voltage	1.5 kV	-
Shielding	no	no
Contact resistance	< 10 mΩ	-
Insulation resistance	≥ 100 MΩ (according to IEC 60512)	≥ 10 GΩ (according to IEC 60512-2)
Mechanical data		
Installation size	M12	M8
Connector type	plug	socket
Configuration	straight	angled
Contact type	male	female
Number of positions (face)	4-pin	4-pin


Coding	A-coded	A-coded
LED	-	with LED
Recommended torque, nut	0.6 Nm	0.4 Nm
Mating cycles	≥ 100 (according to IEC 60512-9a)	≥ 100 (according to IEC 60512-9a)
Way of locking	screw	screw
Body color	black	transparent
Body material	TPU, UL 94	TPU, UL94
Coupling nut material	GD-Zn, Ni	CuZn, Ni
Seal	FPM	FPM
Contact carrier color	red	red
Contact carrier material	PA, UL 94 V-0	TPU GF, UL 94
Contact plating	Ni, Au gal.	Ni, Au gal.
Contact material	CuZn	CuZn
Environmental data		
Special features	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1
RoHS compliant	yes	yes
Ambient temperature (operation)	-30...+85 °C, -22...+185 °F	-30...+80 °C, -22...+176 °F
Protection rating	IP65/67 in screwed condition (according to IEC 60529)	IP65/67 in screwed condition (according to IEC 60529)
Pollution level	3/2 (according to IEC 60664-1)	3/2 (according to IEC 60664-1)

Cable

Electrical data		
Rated voltage	≤ 300 V	
Insulation resistance	≥ 10 GΩ * km	
Wire resistance (signal/24V)	≤ 58.0 Ω/km (20 °C)	
Test voltage	≥ 3000 V	
Mechanical data		
Conductor construction (power)	42 x 0.10 mm	
Cross-section	4 x 0.34 mm ² (AWG 22)	
Min. bending radius, moved	6 x outer cable diameter	
Min. bending radius, moved in drag-chain	10 x outer cable diameter	
Min. bending radius, fixed installation	5 x outer cable diameter	
Weight	31 kg/km (20.8 lb/1000 ft)	
Outer cable diameter	4.7 mm ± 0.15 mm (0.185" ± 0.0059")	

Shielding	no
Use	drag-chain suitable
Max. acceleration	10 m/s ²
Max. speed	5 m/s
Max. number of cycles	10 million at max. 20 m travel distance, 2 million at max. 100 m travel distance
Wall thickness of wire insulation (power)	≥ 0.21 mm
Jacket color	black
Material jacket	PUR (polyurethane)
Wire color code	white, blue, black, brown
Wire insulation material	PP (polypropylene)
Printing on the jacket	Li9Y11Y 4x0,34mm ² E242293 (cULus-Symbol) AWM STYLE 20549 80C 300V AWM I A/B 80C 300V FT2
Printing color	white
Environmental data	
Operation temperature range, moved	-25...+80 °C, -13...+176 °F
Flame-retardant	according to DIN EN 60332-2-2
Halogen-free	DIN VDE 0472 part 815
CE	yes
UL	yes, UL E-file number: E242293

Contact assembly**Dimensions**



A1	49.00 mm
----	----------

B1	27.50 mm
----	----------

B2	19.20 mm
----	----------

Notes

- Depending on the cable length (L), the following length tolerances apply:

0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: $+ 40$ mm | ≥ 4.0 m: $+ 1$ %

- Illustrations similar

- Further cable length on request.

Ordering information

Length

ZK2002-6134-0050	5.00 m
------------------	--------

Accessories

ZB8801-0000	torque wrench for hexagonal plugs, adjustable
-------------	---

ZB8801-0001	torque cable key, M8/wrench size 9, for ZB8801-0000
-------------	---

ZB8801-0002	torque cable key, M12/wrench size 13, for ZB8801-0000
-------------	---

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 04/2022

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.