


ZK2020-3100-3xxx | Power cable, PVC, 4 x 0.34 mm², fixed installation



M8, plug, straight, male, 4-pin, A-coded – open end, 4-wire



Plugs

Electrical data	Head A	Head B
Rated voltage	30 V (according to IEC 61076-2-104)	-
Rated current	4 A at 40°C (leaning on IEC 61076-2-104)	-
Shielding	no	-
Insulation resistance	≥ 10 GΩ (according to IEC 60512-2)	-
Mechanical data		
Installation size	M8	open end
Connector type	plug	-
Configuration	straight	-
Contact type	male	-
Number of positions (face)	4-pin	4-wire
Coding	A-coded	-
Recommended torque, nut	0.4 Nm	-
Mating cycles	≥ 100 (according to IEC 60512-9a)	-
Way of locking	screw	-


Weight per piece	0.028 kg (0.0617 lb)	-
Body color	black	-
Body material	TPU, UL94	-
Coupling nut material	CuZn, Ni	-
Seal	FPM	-
Contact carrier color	red	-
Contact carrier material	TPU GF, UL 94	-
Contact plating	Ni, Au gal.	-
Contact material	CuZn	-
Environmental data		
Special features	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1	-
RoHS compliant	yes	-
Ambient temperature (operation)	-30...+80°C, -22...+176°F	-
Protection rating	IP65/67 in screwed condition (according to IEC 60529)	-
Pollution level	3/2 (according to IEC 60664-1)	-

Cable

Electrical data		
Rated voltage	≤ 300 V	
Insulation resistance	≥ 10 GΩ (according to IEC 60512-2)	
Wire resistance (power)	≤ 58.0 Ω/km	
Test voltage	≥ 3000 V	
Mechanical data		
Conductor construction (power)	42 x 0.10 mm	
Cross-section	4 x 0.34 mm ² (AWG22)	
Outer cable diameter	4.7 mm ± 0.15 mm (0.185" ± 0.0059")	
Min. bending radius, fixed installation	10 x outer cable diameter	
Weight	31 kg/km (20.8 lb/1000 ft)	
Shielding	no	
Use	fixed installation	
Wall thickness of wire insulation (power)	≥ 0.21 mm	
Jacket color	gray	
Material jacket	PVC (polyvinyl chloride)	
Wire color code	white, blue, black, brown	

Wire insulation material	PVC (polyvinyl chloride)
Printing color	white
Environmental data	
Operation temperature range, fixed installation	-25...+80°C, -13...+176°F
Flame-retardant	according to DIN EN 60332-2-2

Contact assembly	
1	braun/brown
2	weiß/white
3	blau/blue
4	schwarz/black

Dimensions	
 <p>The diagram shows a side view of the cable assembly with a connector on the left and a multi-pin connector on the right. Dimension A1 is the length of the main cable body, and A2 is the diameter of the cable. A circular view of the connector shows four pins labeled 1, 2, 3, and 4.</p>	
A1	39.60 mm
A2	Ø 10.1 mm

Notes

- Depending on the cable length (L), the following length tolerances apply:
0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: + 40 mm | ≥ 4.0 m: + 1%
- Illustrations similar
- Further cable length on request.

CE, UL	
UL	yes, UL E-file number: E480185

Ordering information	Length
ZK2020-3100-3010	1.00 m
ZK2020-3100-3050	5.00 m

Accessories	
--------------------	--

ZB8801-0000	torque wrench for hexagonal plugs, adjustable
ZB8801-0001	torque cable key, M8/wrench size 9, for ZB8801-0000



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2024

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.