



ZK2000-7200-0xxx | Sensor cable, PUR, 4 x 0.34 mm², drag chain suitable

M12, socket, straight, female, 5-pin, A-coded – open end, 4-wire + shielding

Plugs


Electrical data	Head A	Head B
Rated voltage	60 V (according to IEC 61076-2-101)	-
Rated current	4 A at 40 °C (according to IEC 61076-2-101)	-
Shielding	no	-
Contact resistance	< 10 mΩ	-
Insulation resistance	≥ 100 MΩ (according to IEC 60512)	-
Mechanical data		
Installation size	M12	open end
Connector type	socket	-
Configuration	straight	-
Contact type	female	-
Number of positions (face)	5-pin	4-wire + shielding
Coding	A-coded	-
Recommended torque, nut	0.6 Nm	-
Mating cycles	≥ 100 (according to IEC 60512-9a)	-
Way of locking	screw	-
Weight per piece	0.023 kg (0.0507 lb)	-
Body colour	black	-
Body material	TPU, UL 94 HB	-
Coupling nut material	GD-Zn, Ni	-
Seal	FPM	-
Contact carrier colour	red	-
Contact carrier material	PA, UL 94 V-0	-
Contact material	CuZn, Ni b/Au 0.2 gal.	-
Environmental data		
Special features	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1	-
RoHS compliant	yes	-
Ambient temperature (operation)	-30...+85 °C, -22...+185 °F	-

Protection class	IP 65/67 in screwed condition (according to IEC 60529)	-
Pollution level	3/2 (according to IEC 60664-1)	-


Cable

Electrical data	
Rated voltage	≤ 300 V
Insulation resistance	10 MΩ * km
Wire resistance (signal/24V)	≤ 58.0 Ω/km (20 °C)
Test voltage	≥ 3000 V
Mechanical data	
Conductor construction (signal/24V)	42 x 0.10 mm
Cross section (power)	4 x 0.34 mm ² (AWG 22) and shield
Cross section (signal)	4 x 0.34 mm ² (AWG22) and shield
Min. bending radius, moved	10 x outer cable diameter
Min. bending radius, fixed installation	5 x outer cable diameter
Weight	45 kg/km (30.2 lb/1000 ft)
Outer cable diameter	5.4 mm ± 0.2 mm (0.213" ±0.0079")
Shielding	aluminium-clad foil, braiding of tinned copper wires
Optical covering factor of shielding	≥ 85%
Use	drag-chain suitable
Max. acceleration	5 m/s ²
Max. speed	1.6 m/s
Max. travel distance	5 m (horizontal with 5 m/s ²), 2 m (vertical with 5 m/s ²)
Max. number of cycles	2 million
Jacket colour	black
Material jacket	PUR (polyurethane)
Wire colour code	brown, white, blue, black
Wire insulation material	PP (polypropylene)
Printing colour	white
Environmental data	
Operation temperature range, moved	-30...+80 °C, -22...+176 °F
Flame-retardant	according to UL 758/1581 (cUL-FT2)
Halogen-free	DIN VDE 0472 part 815

Contact assembly



Dimensions



A1	44.00 mm
A2	20.00 mm

Notes

- Depending on the cable length (L), the following length tolerances apply:
 0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: $+ 40$ mm | ≥ 4.0 m: $+ 1$ %
- Illustrations similar
- Further cable length on request. The last three digits of the ordering information is the cable length in decimeters, e.g. ZKxxxx-xxxx-x020 = cable length 2.00 m

Ordering information	Length
ZK2000-7200-0020	2.00 m
ZK2000-7200-0030	3.00 m
ZK2000-7200-0050	5.00 m
ZK2000-7200-0070	7.00 m
ZK2000-7200-0075	7.50 m
ZK2000-7200-0100	10.00 m
ZK2000-7200-0150	15.00 m
ZK2000-7200-0200	20.00 m

Accessories	
ZB8801-0000	torque wrench for hexagonal plugs, adjustable
ZB8801-0002	torque cable key, M12/wrench size 13, for ZB8801-0000

Beckhoff®, TwinCAT®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 05/2021

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.