

ZK2000-8100-0xxx | Sensor cable, PUR, 8 x 0.25 mm², drag-chain suitable

M12, plug, straight, male, 8-pin, A-coded – open end, 8-wire

Plugs

| Electrical data | Head A | Head B |
|---------------------------------|--|----------|
| Rated voltage | 30 V (according to IEC 61076-2-101) | - |
| Rated current | 2 A at 40 °C (according to IEC 61076-2-101) | - |
| Shielding | yes | - |
| Insulation resistance | ≥ 100 MΩ (according to IEC 60512) | - |
| Mechanical data | | |
| Installation size | M12 | open end |
| Connector type | plug | - |
| Configuration | straight | - |
| Contact type | male | - |
| Number of positions (face) | 8-pin | 8-wire |
| Coding | A-coded | - |
| Recommended torque, nut | 0.6 Nm | - |
| Mating cycles | ≥ 100 (according to IEC 60512-9a) | - |
| Way of locking | screw | - |
| Weight per piece | 0.046 kg (0.1014 lb) | - |
| Body colour | metal | - |
| Body material | GD-Zn, Ni | - |
| Coupling nut material | GD-Zn, Ni | - |
| Seal | elastomers | - |
| O-ring | NBR | - |
| Contact carrier colour | black | - |
| Contact carrier material | PA, UL 94 | - |
| Contact plating | Ni, Au gal. | - |
| Contact material | CuZn | - |
| Environmental data | | |
| RoHS compliant | yes | - |
| Ambient temperature (operation) | -30...+85 °C, -22...+185 °F | - |
| Protection class | IP 65/67 in screwed condition (according to IEC 60529) | - |


Cable

| Electrical data | |
|---|--|
| Rated voltage | ≤ 300 V |
| Insulation resistance | ≥ 1 GΩ * km |
| Wire resistance (signal/24V) | ≤ 78 Ω/km |
| Test voltage | ≥ 3000 V |
| Mechanical data | |
| Conductor construction (signal/24V) | 32 x 0.10 mm |
| Cross section (signal) | 8 x 0.25 mm ² (AWG24) |
| Min. bending radius, moved | 10 x outer cable diameter |
| Min. bending radius, fixed installation | 3 x outer cable diameter |
| Weight | 61.0 kg/km (41.0 lb/1000 ft) |
| Outer cable diameter | 6.6 mm ± 0.2mm (0.259" ± 0.0079") |
| Conductor material (signal/24V) | copper bare |
| Shielding | no |
| Optical covering factor of shielding (total) | no |
| Use | drag-chain suitable |
| Max. acceleration | 10 m/s ² |
| Max. speed | 5 m/s |
| Max. travel distance | 5 m |
| Max. number of cycles | 10 million |
| Jacket colour | black grey (similar to RAL 7021) |
| Material jacket | PUR (polyurethane) |
| Wire colour code | brown, green, yellow, grey, pink, blue, red, white |
| Wire insulation material | PP (polypropylene) |
| Printing colour | white |
| Environmental data | |
| Operation temperature range, moved | -15...+80 °C, +5...+176 °F |
| Operation temperature range, fixed installation | -30...+80 °C, -22...+176 °F |
| Oil resistance | according to DIN EN 60811-2-1 |
| Flame-retardant | according to AWM Style 20549 UL 758/1581 FT2 |
| Halogen-free | according to DIN VDE 0472 part 815, DIN EN 50267-2-1 |

Contact assembly

| | |
|---|-------------|
| 1 | Weiβ/white |
| 2 | Braun/brown |
| 3 | Grün/green |
| 4 | Gelb/yellow |
| 5 | Grau/grey |
| 6 | Rosa/pink |
| 7 | Blau/blue |
| 8 | Rot/red |

Dimensions



| | |
|----|-----------|
| A1 | 49.00 mm |
| A2 | Ø14.50 mm |

Notes

- Depending on the cable length (L), the following length tolerances apply:
 0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: + 40 mm | ≥ 4.0 m: + 1 %
- Illustrations similar
- Further cable length on request. The last three digits of the ordering information is the cable length in decimeters, e.g. ZKxxxx-xxxx-x020 = cable length 2.00 m

| Ordering information | Length |
|----------------------|---------|
| ZK2000-8100-0002 | 0.20 m |
| ZK2000-8100-0003 | 0.30 m |
| ZK2000-8100-0004 | 0.40 m |
| ZK2000-8100-0005 | 0.50 m |
| ZK2000-8100-0010 | 1.00 m |
| ZK2000-8100-0020 | 2.00 m |
| ZK2000-8100-0030 | 3.00 m |
| ZK2000-8100-0050 | 5.00 m |
| ZK2000-8100-0100 | 10.00 m |
| ZK2000-8100-0200 | 20.00 m |

| Accessories | |
|-------------|---|
| ZB8801-0000 | torque wrench for hexagonal plugs, adjustable |
| ZB8801-0002 | torque cable key, M12/wrench size 13, for ZB8801-0000 |

Beckhoff®, TwinCAT®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2021

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.