



ZK7000-0300-1xxx | EtherCAT P cable, AWG22, PUR, fixed installation



M8, plug, angled, male, 4-pin, P-coded – open end, 4-wire + shielding



Plugs

| Electrical data | Head A | Head B |
|----------------------------|--|--------------------|
| Rated voltage | 24 V DC (according to IEC 61076-2-104) | - |
| Rated current | 3 A at 40°C (according to IEC 61076-2-104) | - |
| Shielding | yes | - |
| Insulation resistance | ≥ 100 GΩ (according to IEC 60512) | - |
| Mechanical data | | |
| Installation size | M8 | open end |
| Connector type | plug | - |
| Configuration | angled | - |
| Contact type | male | - |
| Number of positions (face) | 4-pin | 4-wire + shielding |
| Coding | P-coded | - |
| Recommended torque, nut | 0.4 Nm | - |
| Mating cycles | ≥ 100 | - |
| Way of locking | screw | - |

| | | |
|---------------------------------|---|---|
| Body color | black | - |
| Body material | TPU, UL 94 | - |
| Coupling nut material | CuZn, Ni | - |
| Seal | FPM | - |
| Contact carrier color | red | - |
| Contact carrier material | PA, UL 94 | - |
| Contact plating | Ni, Au gal. | - |
| Contact material | CuZn | - |
| Environmental data | | |
| UV resistance | yes | - |
| RoHS compliant | yes | - |
| Ambient temperature (operation) | -40...+85°C, -40...+185°F | - |
| Protection rating | IP65/67 in screwed condition (according to IEC 60529) | - |
| Pollution level | 3/2 (according to IEC 60664-1) | - |


Cable

| | | |
|--|---|--|
| Electrical data | | |
| Rated voltage | max. 300 V (not for high voltage purposes) | |
| Attenuation of shielding | ≥ 65 dB (30...100 MHz) | |
| Insulation resistance | ≥ 500 MΩ * km (DIN EN 50395) | |
| Unbalanced capacitance to ground | ≤ 2000 pF/km | |
| Mutual capacitance | 45 ± 15 pF/m at 800 Hz according to EN 50289-1-5 | |
| Characteristic impedance (Ethernet) | 100 Ω ±5 Ω (100 MHz) (EN 50289-1-11) | |
| Loop resistance | ≤ 110 Ω/km | |
| Dielectric strength wire/wire (Ethernet) | 1 kV (50 Hz, 1 min.) | |
| Dielectric strength wire/shield (Ethernet) | 1 kV AC (50 Hz, 1 min.)/1 kV DC (50 Hz) | |
| Signal running time (Ethernet) | 4.8 ns/m | |
| Electrical parameters (Ethernet) | based on Cat.5 | |
| Test voltage | 1000 V, 50 Hz, 1 min. (wire/wire and wire/screen) | |
| Mechanical data | | |
| Cable structure (Ethernet) | star quad | |
| Conductor construction (Ethernet) | 7-strand | |
| Cross-section (Ethernet) | 1 x 4 x 0.34 mm ² (AWG22) | |
| Outer cable diameter | 5.1 mm ± 0.15 mm (0.200787" ± 0.0059") | |
| Min. bending radius, moved | 8 x outer cable diameter | |


| | |
|---|--|
| Min. bending radius, fixed installation | 5 x outer cable diameter |
| Weight | 50 kg/km (33.6 lb/1000 ft) |
| Conductor material (Ethernet) | copper, tinned |
| Shielding | aluminum-clad foil, braiding of tinned copper wires, coupling |
| Optical covering factor of shielding (Ethernet) | ≥ 85 % |
| Use | fixed installation |
| Jacket color | black (similar to RAL 9005) with red stripe (similar to RAL 3020) |
| Material jacket | PUR (polyurethane) |
| Wire color code | yellow, orange, white, blue |
| Wire insulation material | PO (Polyolefine) |
| Printing on the jacket | Beckhoff Automation GmbH & Co. KG - Germany - EtherCATp Cat5e AWG22/7 E170315 AWM 20549 AWM I/II A/B 80°C 300 V MM/YY RoHS |
| Printing color | white |
| Max. tensile load, dynamic | 20 N/mm ² |
| Max. tensile load, static | 50 N/mm ² |
| Environmental data | |
| Operation temperature range, moved | -30...+80°C, -22...+176°F |
| Operation temperature range, fixed installation | -40...+80°C, -40...+176°F |
| UV resistance | yes |
| Oil resistance | according to DIN EN 60811-404 |
| Flame-retardant | FT-2 |
| CFC-free | yes |
| Halogen-free | DIN VDE 0472 part 815 |
| Silicone-free | yes |
| UL | yes, UL E-file number: E170315 |

| | |
|-------------------------------------|---|
| Attenuation | |
| Max. insertion loss | |
| Frequency [MHz] | 1 4 10 16 20 31.25 62.5 100 |
| [db/100 m] | 3.3 5.3 7.5 9.1 10.1 12.4 17.6 22.5 |
| [db/100 ft] | 1 1.6 2.3 2.8 3.1 3.8 5.4 6.9 |
| Min. near-end crosstalk attenuation | |
| Frequency [MHz] | 1 4 10 16 20 31.25 62.5 100 |
| [db/100 m] | 65 56.3 50.3 47.2 45.8 42.9 38.4 35.3 |
| [db/100 ft] | 19.8 17.2 15.3 14.4 14 13.1 11.7 10.8 |

Contact assembly



Dimensions



| | |
|----|----------|
| A1 | 29.80 mm |
| A2 | 26.30 mm |

Notes

- Depending on the cable length (L), the following length tolerances apply:
 0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: + 40 mm | ≥ 4.0 m: + 1%
- Illustrations similar
- Further cable length on request.

CE, UL

| | |
|----|-----|
| CE | yes |
|----|-----|

Ordering information

Length

| | |
|------------------|--------|
| ZK7000-0300-1010 | 1.00 m |
|------------------|--------|

Accessories

| | |
|-------------|---|
| ZB8801-0000 | torque wrench for hexagonal plugs, adjustable |
|-------------|---|

| | |
|-------------|---|
| ZB8801-0001 | torque cable key, M8/wrench size 9, for ZB8801-0000 |
| ZB8803-0001 | Flange/Panel feed-through for M8 pre-assembled, for fixing the connector, plastic |



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2024

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.