


ZS1052-6610 | Plug control cabinet feed-through CANopen/DeviceNet, IP 67

M12, Wall/panel feed-through, straight, male+female, 5-pin, A-coded

Electrical data	
Rated voltage	150 V
Rated current	4 A
Contact resistance	< 5 mΩ
Insulation resistance	≥ 100 MΩ (according to IEC 60512)
Mechanical data	
Installation size	M12
Connector type	Wall/panel feed-through
Configuration	straight
Contact type	male+female
Number of positions (face)	5-pin
Coding	A-coded
Recommended torque, nut	0.6 Nm
Mating cycles	≥ 100
Way of locking	screw
Contact carrier colour	blue
Contact carrier material	TPU
Contact plating	Au
Contact material	CuZn
Environmental data	
Ambient temperature (operation)	-40...+105 °C, -40...+221 °F
Protection class	IP 67 in screwed condition (according to IEC 60529)
Pollution level	3



A1	47.40 mm
----	----------

Notes

- Illustrations similar

Ordering information

ZS1052-6610	Plug control cabinet feed-through CANopen/DeviceNet, IP 67, M12, male+female, 5-pin, A-coded
-------------	--

Beckhoff®, TwinCAT®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2021

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.