



M8 connector | **4-pole, IP67, field assembly, cable outlet 5,0-6,5mm**

Electrical data	
Rated voltage	30 V
Rated current (40 °C)	4 A
Insulation resistance	≥100MΩ
EMC-Capability	shielded

Mechanical data	
Termination	screw
Wire gauge (mm)	0,14 – 0,50 mm ²
Wire gauge (AWG)	26 - 20
Cable outlet	5,0 – 6,5 mm
Temperature range	-30 °C...+85 °C
Protection level	IP67
Pollution degree	3/2
Contact cycles	≥ 100

Material	
Contact material	CuZn (brass)
Contact surface	Au (gold)
Material of contact body	PA6, UL 94 V-0
Cable sealing	NBR
O-Ring	Silicone / NBR
Material of housing	CuZn (brass nickel plated)

Ordering information	Description
ZS1090-1006	4-pole, IP67, field assembly