



ZS2001-0012 | female header with push-in termination as plug-in connection level, black, 1 x 8 pin, 5 mm grid size, packaging unit = 50



Printed circuit board connector, female, 8-pin



Electrical data	
Rated voltage	320 V
Rated current	16 A
Mechanical data	
Connector type	Printed circuit board connector
Contact type	female
Number of positions (face)	8-pin
Wire termination	Push-in
Recommended torque, nut	0.3 Nm
Way of locking	screw
Weight per piece	14.428 g (0.032 lb)
Body color	black
Contact plating	Tin
Contact material	copper alloy
Max. wire cross-section	AWG14 (2.5 mm ²)
Environmental data	

RoHS compliant	yes
----------------	-----

Protection rating	IP20
-------------------	------

Dimensions

Notes

- Illustrations similar

Ordering information

ZS2001-0012

female header with push-in termination as plug-in connection level, IP20, black, for ELM723x EtherCAT Terminal, slot X2/X3 motor connector up to 16 A, 1 x 8 pin



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 09/2023

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.