

# Explosion protection



ATEX CE 0158 Ex II 3 (1) G Ex ec [ia Ga] IIC T4 Gc  
IECEx Ex ec [ia Ga] IIC T4 Gc

CE 0158 EU-wide harmonised provisions  
related equipment [ ]: marking according to ATEX  
equipment without [ ]: marking of interfaces of the equipment with impact in hazardous area  
use within hazardous areas  
EPL Equipment Protection Level

Device classification				
combustible material	device category	EPL	adequate safety	zone
<b>group I</b>				
methane	M1	Ma	in case of few rare faults	
coal dust	M2	Mb	until device is switched off	
<b>group II</b>				
gas	1G	Ga	in case of few rare faults	0
mist	2G	Gb	in case of predictable faults	1
vapors	3G	Gc	in case of normal use	2
dust	1D	Da	in case of few rare faults	20
	2D	Db	in case of predictable faults	21
	3D	Dc	in case of normal use	22

Temperature classes			
ATEX/IECEx/NEC 505	NEC 500	admissible surface temperature	
gas	dust	marking	
T1	T450 °C	T1	450 °C
T2	T300 °C	T2	300 °C
		T2A	280 °C
		T2B	260 °C
		T2C	230 °C
		T2D	215 °C
T3	T200 °C	T3	200 °C
		T3A	180 °C
		T3B	165 °C
		T3C	160 °C
T4	T135 °C	T4	135 °C
		T4A	120 °C
T5	T100 °C	T5	100 °C
T6	T85 °C	T6	85 °C

NEC 500 Class I Division 1 Groups A, B, C, D T4  
NEC 505 Class I Zone 1 AEx ec [ia Ga] IIC T4 Gc

ATEX: explosion protection for Europe  
IECEx: international explosion protection  
NEC: explosion protection for the USA

explosive atmosphere	explosive hazard	permanent	occasional	short-term
<b>class I</b>				
gas	NEC 500		division 1	division 2
	ATEX/IECEx/NEC 505	zone 0	zone 1	zone 2
<b>class II</b>				
dust	NEC 500		division 1	Division 2
	ATEX/IECEx/NEC 505	zone 20	zone 21	zone 22
<b>class III</b>				
fibers and lint	NEC 500		division 1	division 2
	ATEX/IECEx/NEC 505	zone 20	zone 21	zone 22

	ATEX/IECEx/NEC 505	NEC 500
<b>mining</b>	<b>group I</b>	
methane	I	mining
<b>gas</b>	<b>group II</b>	<b>class I</b>
propane	IIA	CII, Group D
ethylene	IIB	CII, Group C
hydrogen	IIC	CII, Group B
acetylene	IIC	CII, Group A
<b>dust/fibers</b>	<b>group III</b>	<b>class II, III</b>
fibers and lint	IIIA	CIIII
non-conductive dust	IIIB	CII, Group G
conductive dust	IIIC	CII, Group E, F

symbol	protection class	icon	protection principle	gas	dust	standard
Ex o, ob oc	oil immersion		exclusion of explosive atmosphere	zone 1 zone 2		IEC60079-6 EN60079-6 UL60079-6
Ex q, qb	powder filling		prevention of sparks	zone 1		IEC60079-5 EN60079-5 UL60079-5
Ex d, da db dc	flameproof enclosures		spreading prevention	zone 0 zone 1 zone 2		IEC60079-1 EN60079-1 UL60079-1
Ex e, eb ec	increased safety		prevention of sparks	zone 1 zone 2		IEC60079-7 EN60079-7 UL60079-7
Ex m, ma mb mc	compound-filled encapsulation		exclusion of explosive atmosphere	zone 0 zone 1 zone 2	zone 20 zone 21 zone 22	IEC60079-18 EN60079-18 UL60079-18
Ex p, pxb pyb pzc	over-pressure encapsulation		exclusion of explosive atmosphere	zone 1 zone 1 zone 2	zone 21 zone 21 zone 22	IEC60079-2 EN60079-2 UL60079-2
Ex i, ia ib ic	intrinsic safety		ignition power limitation	zone 0 zone 1 zone 2	zone 20 zone 21 zone 22	IEC60079-11 EN60079-11 UL60079-11
Ex op, op is op pr op sh	inherently safe optical radiation protected optical radiation optical systems with interlock		avoid/limit energy transmission of optical radiation	zone 0 zone 1 zone 1	zone 20 zone 21 zone 21	IEC60079-28 EN60079-28
Ex n, nA nC nR nL nP	non-sparking equipment sparking equipment drift-proof housing energy limited simplified over-pressure encapsulation		comparable with Ex e partially Ex d/Ex m protected by enclosures comparable with Ex i comparable with Ex p	zone 2 zone 2 zone 2 zone 2 zone 2		IEC60079-15 EN60079-15 UL60079-15
Ex t, ta tb tc	protected by enclosures		exclusion of explosive atmosphere		zone 20 zone 21 zone 22	IEC60079-31 EN60079-31 UL60079-31

All information is supplied without guarantee

