


ZB3200 | PROFIBUS cable, 12 Mbaud, PVC, 1 x 2 x 0.34 mm², fixed installation



Electrical data	
Rated voltage	250 V
Mutual capacitance wire/wire	max. 30 nF/km (800 Hz)
Insulation resistance	≥ 5GΩ * km
Loop resistance	≤ 115 Ω/km
Test voltage	1500 V (wire/wire and wire/screen)
Mechanical data	
Cable structure	2 wires stranded with 2 drain wires
Cross-section	2 x 0.34 mm ² (AWG22)
Outer cable diameter	8.0 mm ± 0.4 mm (0.3149" ± 0.0157")
Min. bending radius, fixed installation	7.5 x outer cable diameter
Weight	62 kg/km (41.66 lb/1000 ft)
Conductor material	copper bare
Shielding	aluminum-clad foil, braiding of tinned copper wires
Optical covering factor of shielding	≥ 85%
Use	fixed installation
Jacket color	violet (similar to RAL 4001)
Material jacket	PVC (polyvinyl chloride)

Wire color code	red, green
Wire insulation material	PE (polyethylene)
Printing on the jacket	BECKHOFF AUTOMATION ZB3200 PROFIBUS-DP 1x2x0.64 [length in meters] [internal number]
Printing color	black
Environmental data	
Operation temperature range, fixed installation	-40...+80°C, -40...+176°F
Flame-retardant	according to IEC 60332-1-2
Halogen-free	no

Notes

- The following length tolerances apply: 2-3%
- Illustrations similar

Ordering information	Length
ZB3200	sold by the meter



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, ATRO®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, MX-System®, Safety over EtherCAT®, TC/BSD®, TwinCAT®, TwinCAT/BSD®, TwinSAFE®, XFC®, XPlanar® and XTS® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 06/2025

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.