

ZK1052-6200-3xxx | CANopen/DeviceNET cable, PVC, AWG22, fixed installation



M12, socket, straight, female, 5-pin, A-coded – open end, 4-wire + shielding



Plugs

Electrical data	Head A	Head B
Rated voltage	60 V (according to IEC 61076-2-101)	-
Rated current	4 A at 40°C (according to IEC 61076-2-101)	-
Shielding	yes	-
Contact resistance	< 10 mΩ	-
Insulation resistance	≥ 100 MΩ (according to IEC 60512)	-
Mechanical data		
Installation size	M12	open end
Connector type	socket	-
Configuration	straight	-
Contact type	female	-
Number of positions (face)	5-pin	4-wire + shielding
Coding	A-coded	-
Recommended torque, nut	0.6 Nm	-
Mating cycles	≥ 100 (according to IEC 60512-9a)	-

Way of locking	screw	-
Weight per piece	0.023 kg (0.0507 lb)	-
Body color	black	-
Body material	TPU, UL 94 HB	-
Coupling nut material	GD-Zn, Ni	-
Seal	FPM	-
Contact carrier color	red	-
Contact carrier material	PA, UL 94 V-0	-
Contact plating	Ni, Au gal.	-
Contact material	CuZn, Ni b/Au 0.2 gal.	-
Environmental data		
Special features	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1	-
RoHS compliant	yes	-
Ambient temperature (operation)	-30...+85°C, -22...+185°F	-
Protection rating	IP65/67 in screwed condition (according to IEC 60529)	-
Pollution level	3/2 (according to IEC 60664-1)	-

Cable


Electrical data		
Rated voltage	300 V	
Mutual capacitance	37.17 pF/m	
Wire resistance	≤ 54.1 Ω/km	
Mechanical data		
Cross-section	2 x 2 x 0.32 mm ² (AWG22)	
Outer cable diameter	7.24 mm ± 0.2 mm (0.2850" ± 0.0079")	
Shielding	braiding of tinned copper wires	
Optical covering factor of shielding (total)	yes	
Use	fixed installation	
Jacket color	gray	
Material jacket	PVC (polyvinyl chloride)	
Wire color code	white, blue, black, red	
Environmental data		

Operation temperature range, fixed installation -40...+80°C, -40...+185°F


Halogen-free no

UL yes, E-file number: E171202

Contact assembly



Dimensions



A1 44.0 mm

A2 Ø 14.5 mm

Notes

- Depending on the cable length (L), the following length tolerances apply:
0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: + 40 mm | ≥ 4.0 m: + 1%
- Illustrations similar
- Further cable length on request.

CE, UL

UL yes, UL E-file number: E318363

Ordering information

Length

ZK1052-6200-3010 1.00 m

ZK1052-6200-3020	2.00 m
ZK1052-6200-3050	5.00 m
ZK1052-6200-3100	10.00 m
ZK1052-6200-3150	15.00 m

Accessories

ZB8801-0000	torque wrench for hexagonal plugs, adjustable
ZB8801-0002	torque cable key, M12/wrench size 13, for ZB8801-0000
ZB8803-0003	Flange/Panel feed-through for M12 pre-assembled, for fixing the connector, plastic



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2024

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.