

ZK1090-3131-2xxx | EtherCAT cable, PUR, AWG26, fixed installation, comfortable installation at short distances



M8, plug, straight, male, 4-pin, A-coded – M8, plug, straight, male, 4-pin, A-coded



Plugs

| Electrical data | Head A | Head B |
|----------------------------|--|--|
| Rated voltage | 63 V (according to IEC 61076-2-111) | 63 V (according to IEC 61076-2-111) |
| Rated current | 4 A at 40°C (according to IEC 61076-2-104) | 4 A at 40°C (according to IEC 61076-2-104) |
| Shielding | yes | yes |
| Insulation resistance | ≥ 100 GΩ (according to IEC 60512) | ≥ 100 GΩ (according to IEC 60512) |
| Mechanical data | | |
| Installation size | M8 | M8 |
| Connector type | plug | plug |
| Configuration | straight | straight |
| Contact type | male | male |
| Number of positions (face) | 4-pin | 4-pin |
| Coding | A-coded | A-coded |
| Recommended torque, nut | 0.4 Nm | 0.4 Nm |

| | | |
|---------------------------------|---|---|
| Mating cycles | ≥ 100 | ≥ 100 |
| Way of locking | screw | screw |
| Weight per piece | 0.028 kg (0.0617 lb) | 0.028 kg (0.0617 lb) |
| Body color | black | black |
| Body material | TPU, UL94 | TPU, UL94 |
| Coupling nut material | GD-Zn, Ni | GD-Zn, Ni |
| Seal | FPM | FPM |
| Contact carrier color | green | green |
| Contact carrier material | PA 6, UL 94 V0 | PA 6, UL 94 V0 |
| Contact plating | Ni, Au gal. | Ni, Au gal. |
| Contact material | CuZn | CuZn |
| Environmental data | | |
| Special features | halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1 | halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1 |
| RoHS compliant | yes | yes |
| Ambient temperature (operation) | -30...+70°C, -22...+158°F | -30...+70°C, -22...+158°F |
| Protection rating | IP65/67 in screwed condition (according to IEC 60529) | IP65/67 in screwed condition (according to IEC 60529) |
| Pollution level | 3/2 (according to IEC 60664-1) | 3/2 (according to IEC 60664-1) |

Cable

| | | |
|--|---|--|
| Electrical data | | |
| Rated voltage | 30 V (according to IEC 61076-2-101) | |
| Attenuation of shielding | ≥ 50 dB (30...100 MHz) | |
| Insulation resistance | ≥ 500 MΩ/km | |
| Unbalanced capacitance to ground | ≤ 2000 pF/km | |
| Mutual capacitance | nom. 50 nF/km | |
| Characteristic impedance (Ethernet) | 100 Ω ±15 Ω | |
| Loop resistance (Ethernet) | ≤ 260 Ω/km | |
| Unbalanced resistance (Ethernet) | 2 % | |
| Dielectric strength wire/wire (Ethernet) | 1 kV AC (50 Hz, 1 min.)/1 kV DC (50 Hz) | |
| Dielectric strength wire/shield (Ethernet) | 1 kV AC (50 Hz, 1 min.)/1 kV DC (50 Hz) | |
| Signal running time (Ethernet) | 4.8 ns/m | |
| Electrical parameters (Ethernet) | based on Cat.5 | |
| Test voltage | 1000 V, 50 Hz, 1 min. | |
| Mechanical data | | |

| | |
|---|---|
| Cable structure (Ethernet) | star quad |
| Conductor construction (Ethernet) | 7-strand |
| Cross-section (Ethernet) | 1 x 4 x 0.14 mm ² (AWG26) |
| Outer cable diameter | 3.65 mm ± 0.15 mm (0.1496" ± 0.0059") |
| Min. bending radius, moved | 15 x outer cable diameter |
| Min. bending radius, fixed installation | 8 x outer cable diameter, 2.5 x outer cable diameter (fixed with single bend) |
| Weight | 30.0 kg/km (20.2 lb/1000 ft) |
| Conductor material | copper bare |
| Shielding | braiding of tinned copper wires |
| Optical covering factor of shielding (Ethernet) | ≥ 85 % |
| Use | fixed installation |
| Jacket color | green |
| Material jacket | PUR (polyurethane) |
| Wire color code | yellow, orange, white, blue |
| Wire insulation material | PO (Polyolefine) |
| Printing on the jacket | 00000m Beckhoff Automation GmbH & Co. KG - Germany – Industrial Ethernet / EtherCAT ZB9034 Cat5e AWG26/7 E170315 AWM 20963 AWM I A/B 80°C 30V Fa.No.xxxxx |
| Printing color | black |

Environmental data


| | |
|---|--|
| Operation temperature range, moved | -30...+70°C, -22...+158°F |
| Operation temperature range, fixed installation | -40...+80°C, -40...+176°F |
| UV resistance | good |
| Oil resistance | according to DIN EN 60811-404 (7x24 h/90 °C) |
| Acid, lye and solvent resistance | depends on medium, concentration, temperature and duration |
| Flame-retardant | Horizontal flame test according to UL 1581 part 1090 |
| CFC-free | yes |
| Halogen-free | according to IEC 60754 or DIN VDE 0472 part 815 |
| Silicone-free | yes |
| UL | yes, UL E-file number: E170315 |

Attenuation


| | | | | | | | | |
|-------------------------------------|-----|-----|------|------|------|-------|------|------|
| Max. insertion loss | | | | | | | | |
| Frequency [MHz] | 1 | 4 | 10 | 16 | 20 | 31.25 | 62.5 | 100 |
| [db/100 m] | 3.2 | 6.2 | 10.5 | 13.4 | 14.7 | 18.8 | 27.2 | 35.0 |
| [db/100 ft] | 1 | 1.9 | 3.2 | 4.1 | 4.5 | 5.7 | 8.3 | 10.7 |
| Min. near-end crosstalk attenuation | | | | | | | | |

| Frequency [MHz] | 1 | 4 | 10 | 16 | 20 | 31.25 | 62.5 | 100 |
|-----------------|------|------|------|------|------|-------|------|------|
| [db/100 m] | 65 | 56.3 | 50.3 | 47.2 | 45.8 | 42.9 | 38.4 | 35.3 |
| [db/100 ft] | 19.8 | 17.2 | 15.3 | 14.4 | 14 | 13.1 | 11.7 | 10.8 |

Contact assembly



Dimensions



A1 41.00 mm

A2 \varnothing 10.1 mm

B1 41.00 mm

B2 \varnothing 10.1 mm

Notes

- Depending on the cable length (L), the following length tolerances apply:
0 m...<0.2 m: \pm 10 mm | 0.2...4.0 m: + 40 mm | \geq 4.0 m: + 1%
- Illustrations similar
- Further cable length on request.

CE, UL

CE yes

UL yes, UL E-file number: E480185

Ordering information

Length

ZK1090-3131-2001 0.13 m

| | |
|------------------|--------|
| ZK1090-3131-2002 | 0.20 m |
| ZK1090-3131-2003 | 0.30 m |
| ZK1090-3131-2004 | 0.40 m |
| ZK1090-3131-2005 | 0.50 m |
| ZK1090-3131-2006 | 0.60 m |
| ZK1090-3131-2007 | 0.70 m |
| ZK1090-3131-2008 | 0.80 m |
| ZK1090-3131-2009 | 0.90 m |
| ZK1090-3131-2010 | 1.00 m |
| ZK1090-3131-2035 | 3.50 m |
| ZK1090-3131-2050 | 5.00 m |

Accessories

| | |
|-------------|---|
| ZB8801-0000 | torque wrench for hexagonal plugs, adjustable |
| ZB8801-0001 | torque cable key, M8/wrench size 9, for ZB8801-0000 |
| ZB8803-0001 | Flange/Panel feed-through for M8 pre-assembled, for fixing the connector, plastic |



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 03/2024

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.