

ZK1093-9191-3xxx | Industrial Ethernet/EtherCAT patch cable, CAT5, PVC, 1 x 4 x AWG22, fixed installation



RJ45, plug, straight, male, 4-pin – RJ45, plug, straight, male, 4-pin



Plugs

Electrical data	Head A	Head B
Rated voltage	150 V	150 V
Rated current	1.5 A	1.5 A
Shielding	yes	yes
Insulation resistance	≥ 10 GΩ (according to IEC 60512-2)	≥ 10 GΩ (according to IEC 60512-2)
Mechanical data		
Installation size	RJ45	RJ45
Connector type	plug	plug
Configuration	straight	straight
Contact type	male	male
Number of positions (face)	4-pin	4-pin
Mating cycles	≥ 750	≥ 750
Body color	black	black
Body material	TPU, UL 94 HB	TPU, UL 94 HB

Contact carrier material	PC UL 94 V-0	PC UL 94 V-0
Contact plating	Ni, Au gal.	Ni, Au gal.
Contact material	CuZn	CuZn
Environmental data		
RoHS compliant	yes	yes
Ambient temperature (operation)	-40...+70°C, -40...+158°F	-40...+70°C, -40...+158°F
Protection rating	IP20	IP20

Cable

Electrical data		
Rated voltage	600 V	
Insulation resistance	≥ 500 MΩ/km	
Characteristic impedance (Ethernet)	100 Ω ±15 Ω (100 MHz)	
Loop resistance (Ethernet)	≤ 115 Ω/km	
Signal running time (Ethernet)	5.3 ns/m	
Electrical parameters (Ethernet)	based on Cat.5	
Test voltage	≥ 2000 V	
Mechanical data		
Cable structure (Ethernet)	twisted pair	
Conductor construction (Ethernet)	solid	
Cross-section (Ethernet)	1 x 4 x 0.34 mm ² (AWG22)	
Outer cable diameter	6.5 mm ± 0.2 mm (0.2559" ± 0.0079")	
Min. bending radius, moved	7.5 x outer cable diameter	
Min. bending radius, fixed installation	3 x outer cable diameter	
Weight	67 kg/km (45.0 lb/1000 ft)	
Shielding	aluminum-clad foil, braiding of tinned copper wires	
Optical covering factor of shielding (Ethernet)	90 %	
Use	fixed installation	
Jacket color	yellow	
Material jacket	PVC (polyvinyl chloride)	
Wire color code	yellow, orange, white, blue	
Printing color	black	
Environmental data		
Operation temperature range, moved	-40...+75°C, -40...+167°F	
Operation temperature range, fixed installation	-20...+60°C, -4...+140°F	

Ambient temperature, transport/storage -40...+75°C, -40...+167°F

Flame-retardant according to IEC 60332-1-2, according to UL 1685 (CSA FT 4)

UL yes, UL E-file number: E119100

Attenuation


Max. insertion loss

Frequency [MHz]	1	4	10	16	20	31.25	62.5	100
[db/100 m]	1.6	3.2	5.2	6.9	7.8	10.5	15.0	19.5
[db/100 ft]	0.5	1	1.6	2.1	2.4	3.2	4.6	5.9


Min. near-end crosstalk attenuation

Frequency [MHz]	1	4	10	16	20	31.25	62.5	100
[db/100 m]	80	75.0	70.0	65.0	63.0	60.0	55.0	50.0
[db/100 ft]	24.4	22.9	21.3	19.8	19.2	18.3	16.8	15.2

Contact assembly



Dimensions



A1	43.80 mm
B1	43.80 mm

Notes

- Depending on the cable length (L), the following length tolerances apply:
0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: + 40 mm | ≥ 4.0 m: + 1%
- Illustrations similar
- Further cable length on request.

CE, UL	
CE	yes
UL	yes, UL E-file number: E499669

Ordering information	Length
ZK1093-9191-3010	1.00 m
ZK1093-9191-3020	2.00 m
ZK1093-9191-3030	3.00 m
ZK1093-9191-3050	5.00 m
ZK1093-9191-3100	10.00 m
ZK1093-9191-3150	15.00 m
ZK1093-9191-3200	20.00 m
ZK1093-9191-3250	25.00 m
ZK1093-9191-3300	30.00 m
ZK1093-9191-3350	35.00 m
ZK1093-9191-3400	40.00 m
ZK1093-9191-3550	55.00 m

Accessories	
ZK1096-9696-0000	RJ45, socket, straight, female, 8-pin – RJ45, socket, straight, female, 8-pin



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2024

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.