


# ZK7000-0100-1xxx | EtherCAT P cable, PUR, AWG22, fixed installation



M8, plug, straight, male, 4-pin, P-coded – open end, 4-wire + shielding



## Plugs

Electrical data	Head A	Head B
Rated voltage	24 V DC (according to IEC 61076-2-104)	-
Rated current	3 A at 40°C (according to IEC 61076-2-104)	-
Shielding	yes	-
Insulation resistance	≥ 100 GΩ (according to IEC 60512)	-
Mechanical data		
Installation size	M8	open end
Connector type	plug	-
Configuration	straight	-
Contact type	male	-
Number of positions (face)	4-pin	4-wire + shielding
Coding	P-coded	-
Recommended torque, nut	0.4 Nm	-
Mating cycles	≥ 100	-
Way of locking	screw	-

Body color	black	-
Body material	TPU, UL 94	-
Coupling nut material	CuZn, Ni	-
Seal	FPM	-
Contact carrier color	red	-
Contact carrier material	PA, UL 94	-
Contact plating	Ni, Au gal.	-
Contact material	CuZn	-
<b>Environmental data</b>		
UV resistance	yes	-
RoHS compliant	yes	-
Ambient temperature (operation)	-40...+85°C, -40...+185°F	-
Protection rating	IP65/67 in screwed condition (according to IEC 60529)	-
Pollution level	3/2 (according to IEC 60664-1)	-


## Cable

<b>Electrical data</b>		
Rated voltage	max. 300 V (not for high voltage purposes)	
Attenuation of shielding	≥ 65 dB (30...100 MHz)	
Insulation resistance	≥ 500 MΩ * km (DIN EN 50395)	
Unbalanced capacitance to ground	≤ 2000 pF/km	
Mutual capacitance	45 ± 15 pF/m at 800 Hz according to EN 50289-1-5	
Characteristic impedance (Ethernet)	100 Ω ±5 Ω (100 MHz) (EN 50289-1-11)	
Loop resistance	≤ 110 Ω/km	
Dielectric strength wire/wire (Ethernet)	1 kV (50 Hz, 1 min.)	
Dielectric strength wire/shield (Ethernet)	1 kV AC (50 Hz, 1 min.)/1 kV DC (50 Hz)	
Signal running time (Ethernet)	4.8 ns/m	
Electrical parameters (Ethernet)	based on Cat.5	
Test voltage	1000 V, 50 Hz, 1 min. (wire/wire and wire/screen)	
<b>Mechanical data</b>		
Cable structure (Ethernet)	star quad	
Conductor construction (Ethernet)	7-strand	
Cross-section (Ethernet)	1 x 4 x 0.34 mm <sup>2</sup> (AWG22)	
Outer cable diameter	5.1 mm ± 0.15 mm (0.200787" ± 0.0059")	
Min. bending radius, moved	8 x outer cable diameter	


Min. bending radius, fixed installation	5 x outer cable diameter
Weight	50 kg/km (33.6 lb/1000 ft)
Conductor material (Ethernet)	copper, tinned
Shielding	aluminum-clad foil, braiding of tinned copper wires, coupling
Optical covering factor of shielding (Ethernet)	≥ 85 %
Use	fixed installation
Jacket color	black (similar to RAL 9005) with red stripe (similar to RAL 3020)
Material jacket	PUR (polyurethane)
Wire color code	yellow, orange, white, blue
Wire insulation material	PO (Polyolefine)
Printing on the jacket	Beckhoff Automation GmbH & Co. KG - Germany - EtherCATp Cat5e AWG22/7 E170315 AWM 20549 AWM I/II A/B 80°C 300 V MM/YY RoHS
Printing color	white
Max. tensile load, dynamic	20 N/mm <sup>2</sup>
Max. tensile load, static	50 N/mm <sup>2</sup>
<b>Environmental data</b>	
Operation temperature range, moved	-30...+80°C, -22...+176°F
Operation temperature range, fixed installation	-40...+80°C, -40...+176°F
UV resistance	yes
Oil resistance	according to DIN EN 60811-404
Flame-retardant	FT-2
CFC-free	yes
Halogen-free	DIN VDE 0472 part 815
Silicone-free	yes
UL	yes, UL E-file number: E170315

<b>Attenuation</b>	
Max. insertion loss	
Frequency [MHz]	<b>1      4      10      16      20      31.25      62.5      100</b>
[db/100 m]	3.3    5.3    7.5    9.1    10.1    12.4    17.6    22.5
[db/100 ft]	1      1.6    2.3    2.8    3.1    3.8    5.4    6.9
Min. near-end crosstalk attenuation	
Frequency [MHz]	<b>1      4      10      16      20      31.25      62.5      100</b>
[db/100 m]	65    56.3    50.3    47.2    45.8    42.9    38.4    35.3
[db/100 ft]	19.8    17.2    15.3    14.4    14      13.1    11.7    10.8

## Contact assembly



## Dimensions



A1	41.00 mm
A2	Ø10.10 mm

## Notes

- Depending on the cable length (L), the following length tolerances apply:  
0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: + 40 mm | ≥ 4.0 m: + 1%
- Illustrations similar
- Further cable length on request.

## CE, UL

CE	yes
----	-----

## Ordering information

Ordering information	Length
ZK7000-0100-1010	1.00 m
ZK7000-0100-1100	10.00 m

## Accessories

ZB8801-0000	torque wrench for hexagonal plugs, adjustable
ZB8801-0001	torque cable key, M8/wrench size 9, for ZB8801-0000
ZB8803-0001	Flange/Panel feed-through for M8 pre-assembled, for fixing the connector, plastic



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2024

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.