

# ZK2003-91D1-3xxx | Sensor, cable, shielded, PVC, 4 x 2 x AWG26, fixed installation, grey



RJ45, push-pull V4, plug, straight, male, 8-pin – RJ45, plug, straight, male, 8-pin



## Plugs

Electrical data	Head A	Head B
Rated voltage	50 V AC/60 V DC	24 V
Rated current	1.3 A at 40°C	1.3 A at 40°C
Voltage proof (contact/contact)	-	≥ 1000 V DC
Shielding	yes	yes
Transmission characteristics	Cat.6 Class EA up to 500 MHz, 10/100 Mbit/s, 1/10 Gbit/s	-
Mechanical data		
Accessories type	Connectors for field assembly	-
Installation size	RJ45, push-pull V4	RJ45
Connector type	plug	plug
Configuration	straight	straight
Contact type	male	male
Number of positions (face)	8-pin	8-pin


Wire termination	IDC	-
Mating cycles	≥ 750	≥ 750
Way of locking	push-pull	locking pin
Body color	black	green
Body material	plastic	plastic
Contact carrier color	yellow	transparent/blue
Contact carrier material	-	PC, UL 94 V-2
Contact material	copper alloy	Phosphor-Bronze gold plated
Max. wire cross-section	AWG27 ... AWG22 (0.1 mm <sup>2</sup> ... 0.34 mm <sup>2</sup> )	-
Max. cable outer diameter	4.5...10.0 mm	-
<b>Environmental data</b>		
Special features	-	Cat.6A
UV resistance	yes	-
RoHS compliant	yes	yes
Ambient temperature (operation)	-40...+70°C, -40...+158°F	-40...+80°C, -40...+176°F
Protection rating	IP65/67	IP20
Approvals	UL, CSA	-

## Cable

<b>Electrical data</b>	
<b>Mechanical data</b>	
Cable structure	4 x 2 x AWG26
Cable structure (Ethernet)	twisted shielded pair
Conductor construction (Ethernet)	7-strand
Cross-section (Ethernet)	4 x 2 x 0.14 mm <sup>2</sup> (AWG26)
Outer cable diameter	6.2 mm ± 0.2mm (0.244" ± 0.0079")
Min. bending radius, moved	15 x outer cable diameter
Min. bending radius, fixed installation	7.5 x outer cable diameter
Weight	55 kg/km (36.96 lb/1000 ft)
Conductor material (Ethernet)	tinned copper
Shielding	braiding of tinned copper wires
Use	fixed installation
UL-Style	UL758 (AWM) Style 2464, CSA C22.2 No. 210 - AWM I/II A/B
Jacket color	gray
Material jacket	PVC (polyvinyl chloride)
Wire insulation material	PVC (polyvinyl chloride)

Environmental data	
Operation temperature range, moved	-10...+80°C, 14...+176°F
Operation temperature range, fixed installation	-40...+80°C, -40...+185°F
Oil resistance	yes
LABS-free	yes
Flame-retardant	according to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2, UL VW-1, CSA FT1
Halogen-free	no
Silicone-free	yes

Contact assembly	
1	weiß/white
2	braun/brown
3	grün/green
6	gelb/yellow
4	grau/grey
5	rosa/pink
7	blau/blue
8	rot/red

Dimensions	
	
A1	68.0 mm
A2	23.8 mm
A3	20.4 mm
B1	46.2 mm
B2	13.3 mm

## Notes

- Depending on the cable length (L), the following length tolerances apply:  
0.5 m: ± 20 mm | 1.0 m ... 5.0 m: ± 40 mm | 7.5 m ... 50.0 m: ± 1%
- Illustrations similar
- Further cable length on request.

## CE, UL

CE yes

## Ordering information

## Length

ZK2003-91D1-3005 0.50 m

ZK2003-91D1-3010 1.00 m

ZK2003-91D1-3015 1.50 m

ZK2003-91D1-3020 2.00 m

ZK2003-91D1-3025 2.50 m

ZK2003-91D1-3030 3.00 m

ZK2003-91D1-3040 4.00 m

ZK2003-91D1-3050 5.00 m

Further length on request



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, ATRO®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, MX-System®, Safety over EtherCAT®, TC/BSD®, TwinCAT®, TwinCAT/BSD®, TwinSAFE®, XFC®, XPlanar® and XTS® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 06/2025

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.