

# ZK2020-3134-3xxx | Power cable, PVC, 4 x 0.34 mm<sup>2</sup>, fixed installation



M8, plug, straight, male, 4-pin, A-coded – M8, socket, angled, female, 4-pin, A-coded



## Plugs

Electrical data	Head A	Head B
Rated voltage	30 V (according to IEC 61076-2-104)	30 V (according to IEC 61076-2-104)
Rated current	4 A at 40°C (leaning on IEC 61076-2-104)	4 A at 40°C (leaning on IEC 61076-2-104)
Shielding	no	no
Insulation resistance	≥ 10 GΩ (according to IEC 60512-2)	≥ 10 GΩ (according to IEC 60512-2)
Mechanical data		
Installation size	M8	M8
Connector type	plug	socket
Configuration	straight	angled
Contact type	male	female
Number of positions (face)	4-pin	4-pin
Coding	A-coded	A-coded
Recommended torque, nut	0.4 Nm	0.4 Nm
Mating cycles	≥ 100 (according to IEC 60512-9a)	≥ 100 (according to IEC 60512-9a)

Way of locking	screw	screw
Weight per piece	0.028 kg (0.0617 lb)	-
Body color	black	black
Body material	TPU, UL94	TPU, UL94
Coupling nut material	CuZn, Ni	CuZn, Ni
Seal	FPM	FPM
Contact carrier color	red	red
Contact carrier material	TPU GF, UL 94	TPU GF, UL 94
Contact plating	Ni, Au gal.	Ni, Au gal.
Contact material	CuZn	CuZn
<b>Environmental data</b>		
Special features	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1
RoHS compliant	yes	yes
Ambient temperature (operation)	-30...+80°C, -22...+176°F	-30...+80°C, -22...+176°F
Protection rating	IP65/67 in screwed condition (according to IEC 60529)	IP65/67 in screwed condition (according to IEC 60529)
Pollution level	3/2 (according to IEC 60664-1)	3/2 (according to IEC 60664-1)

## Cable

<b>Electrical data</b>		
Rated voltage	≤ 300 V	
Insulation resistance	≥ 10 GΩ (according to IEC 60512-2)	
Wire resistance (power)	≤ 58.0 Ω/km	
Test voltage	≥ 3000 V	
<b>Mechanical data</b>		
Conductor construction (power)	42 x 0.10 mm	
Cross-section	4 x 0.34 mm <sup>2</sup> (AWG22)	
Outer cable diameter	4.7 mm ± 0.15 mm (0.185" ± 0.0059")	
Min. bending radius, fixed installation	10 x outer cable diameter	
Weight	31 kg/km (20.8 lb/1000 ft)	
Shielding	no	
Use	fixed installation	
Wall thickness of wire insulation (power)	≥ 0.21 mm	
Jacket color	gray	
Material jacket	PVC (polyvinyl chloride)	

Wire color code white, blue, black, brown

Wire insulation material PVC (polyvinyl chloride)


Printing color white

#### Environmental data


Operation temperature range, fixed installation -25...+80°C, -13...+176°F

Flame-retardant according to DIN EN 60332-2-2

#### Contact assembly



#### Dimensions



A1 39.60 mm

A2  $\varnothing$  10.1 mm

B1 27.50 mm

B2 19.20 mm

## Notes

- Depending on the cable length (L), the following length tolerances apply:  
0 m...<0.2 m:  $\pm$  10 mm | 0.2...4.0 m: + 40 mm |  $\geq$  4.0 m: + 1%
- Illustrations similar
- Further cable length on request.

#### Ordering information

#### Length

ZK2020-3134-3010

1.00 m

**Accessories**

ZB8801-0000	torque wrench for hexagonal plugs, adjustable
ZB8801-0001	torque cable key, M8/wrench size 9, for ZB8801-0000



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2024

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.