


ZK2030-1600-0xxx | Power cable, PVC, 5 x 1.5 mm² (AWG16), fixed installation





7/8"-16 UN, flange front assembly with wires, straight, female, 5-pin, A-coded
– open end, 5-wire



Plugs

Electrical data	Head A	Head B
Rated voltage	300 V (according to IEC 60664-1)	-
Rated current	12 A at 40°C (according to IEC 60512-3), 10 A (according to UL2238)	-
Rated impulse voltage	2.5 kV	-
Shielding	no	-
Insulation resistance	≥ 100 MΩ (according to IEC 60512)	-
Mechanical data		
Installation size	7/8"-16 UN	open end
Connector type	flange front assembly with wires	-
Configuration	straight	-
Contact type	female	-
Number of positions (face)	5-pin	5-wire
Coding	A-coded	-

Mating cycles	≥ 100 (according to IEC 60512-9a)	-
Way of locking	screw	-
Body color	black	-
Body material	CuZn, Ni	-
Coupling nut material	CuZn, Ni	-
Seal	FPM	-
Contact carrier color	red	-
Contact carrier material	TPU, UL 94 HB	-
Contact plating	Ni, Au gal.	-
Contact material	CuZn	-
Environmental data		
Special features	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1	-
RoHS compliant	yes	-
Ambient temperature (operation)	-40...+80°C, -40...+176°F	-
Protection rating	IP65/67 in screwed condition (according to IEC 60529)	-
Pollution level	3/2 (according to IEC 60664-1)	-

Contact assembly**Dimensions**

A1

24.80 mm


A2

23.80 mm

Notes

- Depending on the cable length (L), the following length tolerances apply:
0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: $+ 40$ mm | ≥ 4.0 m: $+ 1\%$
- Illustrations similar
- Further cable length on request.

Installation dimensions



Minimum wall thickness 2,5 mm,
alternativ panel cut out d=18,8 /
Minimale Wandstärke 2,5 mm,
alternativ Frontplattenausschnitt d=18,8

Ordering information

Length

ZK2030-1600-0010	1.00 m
ZK2030-1600-0030	3.00 m

Further length on request

Accessories

ZK2030-1112-0000	Power adapter, 7/8", flange, straight, male, 5-pin – 7/8", flange, straight, female, 5-pin
------------------	--



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, ATRO®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, MX-System®, Safety over EtherCAT®, TC/BSD®, TwinCAT®, TwinCAT/BSD®, TwinSAFE®, XFC®, XPlanar® and XTS® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 09/2025

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.