

# ZK7780-1800-0xxx | B23, power cable, PUR, 3 G 6 mm<sup>2</sup>, drag-chain suitable, key 2



B23, plug, straight, male+blanking plug, pins 2+PE, Power – open end, 3-wire



## Plugs

| Electrical data                  | Head A                                 | Head B   |
|----------------------------------|----------------------------------------|----------|
| Rated voltage (power)            | 630 V AC / 850 V DC, 600V AC / DC (UL) | -        |
| Rated current (power)            | 28 A at 40°C                           | -        |
| Rated impulse voltage (power)    | 6.0 kV                                 | -        |
| Rated impulse voltage (Ethernet) | 1.0 kV                                 | -        |
| Contact resistance               | < 5 mΩ                                 | -        |
| Insulation resistance            | ≥ 100 MΩ (according to IEC 60512)      | -        |
| Mechanical data                  |                                        |          |
| Installation size                | B23                                    | open end |
| Connector type                   | plug                                   | -        |
| Configuration                    | straight                               | -        |
| Contact type                     | male+blanking plug                     | -        |
| Number of positions (face)       | pins 2+PE                              | 3-wire   |
| Coding                           | Power                                  | -        |
| Mechanical coding                | key 2 (user-defined voltage)           | -        |


|                                 |                                                                                                              |   |
|---------------------------------|--------------------------------------------------------------------------------------------------------------|---|
| Wire termination                | crimp connection                                                                                             | - |
| Mating cycles                   | $\geq 100$                                                                                                   | - |
| Way of locking                  | bayonet                                                                                                      | - |
| Body color                      | metal                                                                                                        | - |
| Body material                   | CuZn, Ni                                                                                                     | - |
| Coupling nut material           | GD-Zn, Ni                                                                                                    | - |
| Contact carrier material        | PA, UL 94                                                                                                    | - |
| Contact carrier color (power)   | red                                                                                                          | - |
| Contact plating                 | Au over Ni                                                                                                   | - |
| Contact material                | copper alloy                                                                                                 | - |
| Max. wire cross-section         | 10.0 mm <sup>2</sup>                                                                                         | - |
| Max. cable outer diameter       | 11.0...13.0 mm                                                                                               | - |
| <b>Environmental data</b>       |                                                                                                              |   |
| Shock resistance                | 50 g (490 m/s <sup>2</sup> ) conforms to IEC 60512-6c, 11 ms; 18 shocks per direction, 3 axes                | - |
| Vibration resistance            | 5 g (50 m/s <sup>2</sup> ) conforms to IEC 60512-6d, 10 Hz ... 500 Hz; 10 cycles per axis; 6 h full duration | - |
| RoHS compliant                  | yes                                                                                                          | - |
| Ambient temperature (operation) | -30...+80°C, -22...+176°F                                                                                    | - |
| Protection rating               | IP65/67 in screwed condition (according to IEC 60529)                                                        | - |
| Pollution level                 | 3/2 (according to IEC 60664-1)                                                                               | - |

## Cable


|                                         |                                                             |  |
|-----------------------------------------|-------------------------------------------------------------|--|
| <b>Electrical data</b>                  |                                                             |  |
| Rated voltage                           | 600 V/1000 V                                                |  |
| Test voltage                            | 4000 V                                                      |  |
| <b>Mechanical data</b>                  |                                                             |  |
| Conductor construction                  | fine stranded according to VDE 0295 cl. 6 / IEC 60228 cl. 6 |  |
| Cross-section                           | 3 G 6 mm <sup>2</sup> (AWG10)                               |  |
| Outer cable diameter                    | 12.6 mm                                                     |  |
| Min. bending radius, moved              | 7.5 x outer cable diameter                                  |  |
| Min. bending radius, fixed installation | 4 x outer cable diameter                                    |  |
| Conductor material                      | copper bare                                                 |  |
| Shielding                               | no                                                          |  |
| Use                                     | drag-chain suitable                                         |  |
| Max. acceleration                       | 80 m/s <sup>2</sup>                                         |  |

|                                                 |                                                      |
|-------------------------------------------------|------------------------------------------------------|
| Max. speed                                      | free-standing: 10 m/s, sliding: 6 m/s                |
| Max. travel distance                            | 400 m                                                |
| Jacket color                                    | black (similar to RAL9005)                           |
| Material jacket                                 | TPE                                                  |
| Material jacket, further characteristics of     | halogen-free, flame-retardant, matt and low adhesion |
| Wire color code                                 | black, green/yellow                                  |
| Wire insulation material                        | TPE (thermoplastic elastomer)                        |
| Printing color                                  | white                                                |
| <b>Environmental data</b>                       |                                                      |
| Operation temperature range, moved              | -40...+90°C, -40...+194°F                            |
| Operation temperature range, fixed installation | -50...+90°C, -58...+194°F                            |
| UV resistance                                   | yes                                                  |
| Oil resistance                                  | 168 h 100°C (according to DIN EN 60811-404)          |
| Flame-retardant                                 | according to IEC 60332-1, cable flame test, FT1      |
| Halogen-free                                    | yes                                                  |
| Silicone-free                                   | yes                                                  |
| RoHS compliant                                  | yes                                                  |
| CE                                              | yes                                                  |
| Approvals                                       | UL, CSA - cURus 80°C 1000V                           |

#### Pin assignment



#### Dimensions



|    |       |
|----|-------|
| A1 | 83 mm |
| A2 | 29 mm |

### Mechanical coding

Mechanical keying uses defined keyways that only allow insertion and subsequent locking rotation when correctly aligned. For more information, please refer to the [keying guide for correct use](#).

### Notes

- Depending on the cable length (L), the following length tolerances apply:  
0 m...3.0 m: + 100 mm | 3.0...10.0 m: ± 100 mm | ≥ 10.0 m: ± 2%
- Illustrations similar
- Further cable length on request. The last three digits of the ordering information is the cable length in decimeters, e.g. ZKxxxx-xxxx-x020 = cable length 2.00 m
- The design of the pre-assembled cable shown here may differ from the products supplied, despite technically identical specifications.

| CE, UL |     |
|--------|-----|
| CE     | yes |

| Ordering information | Length  |
|----------------------|---------|
| ZK7780-1800-0030     | 3.00 m  |
| ZK7780-1800-0050     | 5.00 m  |
| ZK7780-1800-0080     | 8.00 m  |
| ZK7780-1800-0100     | 10.00 m |
| ZK7780-1800-0150     | 15.00 m |
| ZK7780-1800-0200     | 20.00 m |

Further length on request



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, ATRO®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, MX-System®, Safety over EtherCAT®, TC/BSD®, TwinCAT®, TwinCAT/BSD®, TwinSAFE®, XFC®, XPlanar® and XTS® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 07/2026

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.