


C9900-K927...K929 | Display cable, shielded, PVC, fixed installation, black



Mini DisplayPort, push-pull V4, plug, straight, male, 20-pin – DVI-D, plug, straight, male, 24 + 1-pin



Plugs


Electrical data	Head A	Head B
Rated voltage	30 V	40 V (AC)
Rated current	0.5 A	1.5 A
Dielectric strength	-	500 V
Shielding	yes	yes
Contact resistance	< 30 mΩ	< 30 mΩ
Mechanical data		
Installation size	Mini DisplayPort, push-pull V4	DVI-D
Connector type	plug	plug
Configuration	straight	straight
Contact type	male	male
Number of positions (face)	20-pin	24 + 1-pin
Mating cycles	≥ 100	-
Way of locking	push-pull	screw

Body color	black	black
Body material	Plastic	PBT
Contact carrier color	black	black
Contact plating	Au over Ni	Au
Contact material	copper alloy	phosphorus bronze
Environmental data		
RoHS compliant	yes	yes
Protection rating	IP65/67	IP20

Cable

Electrical data		
Operating voltage	30 V	
Wire resistance	$\leq 381 \Omega/\text{km}$ (20 °C)	
Test voltage	500 V (AC), 1 min.	
Mechanical data		
Cross-section	5 x 2 x AWG30 + 4 x AWG30	
Outer cable diameter	6.5 mm \pm 0.2 mm (0.2559" \pm 0.0079")	
Min. bending radius, fixed installation	10 x outer cable diameter	
Conductor material	copper, tinned	
Shielding	yes	
Use	fixed installation	
Jacket color	black	
Material jacket	TPE (FRNC)	
Wire color code	white, brown, white, red, white, green, white, blue, white, yellow, brown, red, orange, yellow	
Wire insulation material	PE (polyethylene), PO (Polyolefine)	
Environmental data		
Operation temperature range, fixed installation	0...+80 °C, +32...+176 °F	
Halogen-free	yes	
RoHS compliant	yes	

Dimensions		
-------------------	--	--



A1	78.3 mm
A2	23.8 mm
A3	20.4 mm
B1	54,0 mm
B2	12,1 mm
B3	39,0 mm

Notes

- Depending on the cable length (L), the following length tolerances apply:
0.5 m: ± 30 mm | 1.0 m ... 3.0 m: ± 50 mm | 5.0 m: ± 100 mm
- Illustrations similar
- Further cable length on request.

CE, UL	
CE	yes

Ordering information	Length
C9900-K927	1.00 m
C9900-K928	3.00 m
C9900-K929	5.00 m



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 01/2023

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.