


C9900-K959...K969 | Industrial Ethernet/EtherCAT cable, PUR, 4 x 2 x AWG26/7, fixed installation, green, Cat.6A



RJ45, push-pull V4, plug, straight, male, 8-pin – RJ45, plug, straight, male, 8-pin



Plugs

Electrical data	Head A	Head B
Rated voltage	50 V AC / 60 V DC	24 V
Rated current	1.3 A at 40°C	1.3 A at 40°C
Voltage proof (contact/contact)	≥ 1000 V DC	≥ 1000 V DC
Voltage proof (contact/shield)	≥ 1500 V DC	-
Shielding	yes	yes
Mechanical data		
Installation size	RJ45, push-pull V4	RJ45
Connector type	plug	plug
Configuration	straight	straight
Contact type	male	male
Number of positions (face)	8-pin	8-pin
Mating cycles	≥ 750	≥ 750


Way of locking	push-pull	locking pin
Weight per piece	0.049 kg (0.1080 lb)	-
Body color	black	green
Body material	thermoplastic	plastic
Contact carrier color	transparent/blue	transparent/blue
Contact carrier material	UL 94 V-0	PC, UL 94 V-2
Contact material	CuZn, Ni b/Au	Phosphor-Bronze gold plated
Environmental data		
Special features	Cat.6A	Cat.6A
UV resistance	yes	-
RoHS compliant	yes	yes
Ambient temperature (operation)	-40...+70 °C, -40...+158 °F	-40...+80 °C, -40...+176 °F
Protection rating	IP65/67	IP20
Approvals	UL, CSA	-

Cable


Electrical data		
Operating voltage	max. 100 V	
Insulation resistance	≥ 500 MΩ/km	
Wire resistance	≤ 290 Ω/km (20 °C)	
Electrical parameters	Cat.6A	
Test voltage	700 V, 50 Hz, 1 min. (wire/wire and wire/screen)	
Mechanical data		
Conductor construction	7 strand	
Cross-section	4 x 2 x AWG26/7	
Min. bending radius, moved	10 x outer cable diameter	
Min. bending radius, fixed installation	5 x outer cable diameter	
Weight	46 kg/km (101,41 lb/1000 ft)	
Outer cable diameter	6.7 mm ± 0.3 mm (0.2637" ± 0.0118")	
Shielding	braiding of tinned copper wires	
Optical covering factor of shielding (total)	≥ 70 %	
Use	fixed installation	
UL-Style conductor	AWM 21815 (80°C/300V)	
Jacket color	green	
Material jacket	PUR (polyurethane)	

Wire color code	white / blue, white / orange, white / green, white / brown
Wire insulation material	PUR (polyurethane)
Environmental data	
Operation temperature range, moved	-40...+80 °C, -40...+176 °F
Operation temperature range, fixed installation	-40...+80 °C, -40...+176 °F
UV resistance	yes
Oil resistance	according to DIN EN 60811-404 (7x24 h/90 °C)
Flame-retardant	according to IEC 60332-1-2, UL 1581 Sec. 1090 (H)
Halogen-free	yes
RoHS compliant	yes acc. to directive 2011/65/EC
Approvals	UL listed

Contact assembly



Dimensions



A1	68.0 mm
A2	23.8 mm
A3	20.4 mm
B1	46.2 mm
B2	13.3 mm

B3	14.0 mm
----	---------

Notes

- Depending on the cable length (L), the following length tolerances apply:
0.5 m: ± 20 mm | 1.0 m ... 5.0 m: ± 40 mm | 7.5 m ... 50.0 m: $\pm 1\%$
- Illustrations similar
- Further cable length on request.

CE, UL

CE	yes
----	-----

Ordering information

Length

C9900-K959	0.50 m
C9900-K960	1.00 m
C9900-K961	3.00 m
C9900-K962	5.00 m
C9900-K963	7.50 m
C9900-K964	10.00 m
C9900-K965	15.00 m
C9900-K966	20.00 m
C9900-K967	30.00 m
C9900-K968	40.00 m
C9900-K969	50.00 m



Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 04/2022

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.