





ZS1090-1017 | Socket, field assembly, shielded

M8, socket, angled, female, 4-pin, A-coded



Electrical data	
Rated voltage	50 V AC/60 V DC (according to IEC 61076-2-104)
Rated current	4 A at 40°C (according to IEC 61076-2-104)
Shielding	yes
Insulation resistance	≥ 100 MΩ (according to IEC 60512)
Mechanical data	
Accessories type	Connectors
Installation size	M8
Connector type	socket
Configuration	angled
Contact type	female
Number of positions (face)	4-pin
Coding	A-coded
Wire termination	screw connection
Recommended torque, nut	0.4...0.5 Nm
Mating cycles	≥ 100
Way of locking	screw

Weight	0.028 kg (0.0617 lb)
Body color	metal
Body material	CuZn, Ni
Coupling nut material	CuZn, Ni
Seal	EPDM
O-ring	EPDM
Contact carrier color	black
Contact carrier material	PA66 UL94 HB
Contact plating	Au over Ni
Contact material	nickel/gold plated
Max. wire cross-section	AWG20 (0.5 mm ²)
Max. cable outer diameter	4.9...6.5 mm
Environmental data	
Special features	RoHS compliant and lead-free
UV resistance	yes
RoHS compliant	yes
Ambient temperature (operation)	-40...+85°C, -40...+185°F
Protection rating	IP67 in screwed condition (according to IEC 60529)
Pollution level	3
UL	yes, UL E-file number: E480185

Dimensions	
	
A1	~34.5 mm
A2	14.0 mm
A3	~31.0 mm
A4	~13.5 mm

Notes

- Illustrations similar

Ordering information

ZS1090-1017

socket, field assembly, Ethernet/EtherCAT, M8, IP65/67, angled, female, 4-pin, A-coded, Ø 4.9...6.5 mm

Accessories

ZB8801-0000

torque wrench for hexagonal plugs, adjustable

ZB8801-0002

torque cable key, M12/wrench size 13, for ZB8801-0000



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, ATRO®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, MX-System®, Safety over EtherCAT®, TC/BSD®, TwinCAT®, TwinCAT/BSD®, TwinSAFE®, XFC®, XPlanar® and XTS® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 01/2026

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressively agreed in the terms of contract.