


ZS1091-0001 | Plug, PushPull, LC Duplex, Multimode, IP67, 2-pin, packaging=10




Fiber optic connector, plug, straight, 2-pin



Electrical data	
Mechanical data	
Accessories type	Connectors
Installation size	Fiber optic connector
Connector type	plug
Configuration	straight
Number of positions (face)	2-pin
Wire termination	crimp connection
Mating cycles	≥ 200
Way of locking	push-pull V4
Body color	black
Body material	plastic
Max. cable outer diameter	4.9 ... 8.6 mm
Environmental data	
RoHS compliant	yes
Ambient temperature (operation)	-40...+70°C, -40...+158°F
Protection rating	IP67

Dimensions



A1	20.00 mm
A2	approx. 49 mm
A3	6.25 mm

Notes

- Illustrations similar

Ordering information

ZS1091-0001	Plug, PushPull, LC Duplex, Multimode, IP67, 2-pin
-------------	---



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, ATRO®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, MX-System®, Safety over EtherCAT®, TC/BSD®, TwinCAT®, TwinCAT/BSD®, TwinSAFE®, XFC®, XPlanar® and XTS® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 06/2025

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.