



Mining And Surface Certification (Pty) Ltd

2015/021934/07

THIS CERTIFICATE IS ISSUED AS AN I.A. CERTIFICATE IN TERMS OF THE MINE HEALTH AND SAFETY ACT, ACT NO 29 OF 1996 (AND REGULATIONS), THE OCCUPATIONAL HEALTH AND SAFETY ACT (ACT 85 OF 1993) AND REGULATION 17 OF THE ELECTRICAL MACHINERY REGULATIONS

IA CERTIFICATE	MASC S/26-8144X	Issue	0
Issue Date	02 April 2026	Expiry Date	02 April 2029
** Based on Certificate No	IECEx DEK 17.0020X	Issue / Variations / Amendment	0
Requested by	Beckhoff Automation (Pty) Ltd 7 Ateljee Street, Randpark Ridge, Randburg		
Manufacturer	Beckhoff Automation GmbH & Co. KG Hülsthorstweg 20, 33415 Verl, Germany		
Description	Embedded PC Series CX8000 for use in I/O and Fieldbus systems. See Base Certificate** Annex for the electrical data of the supply and the input and output circuits, the ambient temperature range and the temperature class of the modules that shall be taken from Table 1.		
Equipment	Embedded PC	Type	CX8000
MARKING: Original marking as per certificate ** remains applicable. IA number must be added.	Type: Ex Marking: IA Number: Warnings:	Embedded PC Series CX8000 Ex nA IIC T4 Gc and Ex tc IIIC T135 °C Dc MASC S/26-8144X (To be additionally marked on equipment) See Base Certificate ** (original marking must be applied)	
Quality Assurance report (QAR) / Notification (QAN):	DE/BVS/QAR16.0010/10		
Compliance: The equipment as described above has been allocated the rating <u>Explosion Protected 'as above'</u> utilizing the SANS/IEC Standards: <ul style="list-style-type: none"> SANS (IEC) 60079-0: 2019 Equipment - General requirements SANS (IEC) 60079-15: 2010 Equipment protection by type of protection "n" SANS (IEC) 60079-31: 2014 Equipment dust ignition protection by enclosure "t" <i>Note: This certificate covers only the listed standards and does not imply compliance to any other standard, related or inferred. It is up to the manufacturer to ensure that the product complies to all relevant standards for the application.</i>			
Specific conditions of use "X": <ul style="list-style-type: none"> Refer to Annex A below for more details. 			
Conditions of manufacture: <ul style="list-style-type: none"> Refer to Annex A below for more details. 			
 S. JORDAAN TECHNICAL SPECIALIST		 N. VILOJEN TECHNICAL OFFICER	
<small>This certificate covers all units sold as long as the QAR/QAN remains valid.</small>			
<small>According to the relevant requirements of the MHS Act and the OHS Act, production units of explosion protected equipment are required to comply with third party quality assurance (an approved mark scheme or batch testing by an accredited test laboratory).</small>			

Apparatus in hazardous locations is subject to the following provisions as applicable, which shall be adhered to:

- SANS 10086 requirements;
- Any conditions mentioned in the above certificate;
- Any relevant requirements of the MHS Act;

Any restrictions and conditions enforced by the chief inspector of mines, principal inspector (Group I equipment) or chief inspector of factories (Group II equipment).

This certificate may only be reproduced in full
The certificate is not transferable and remains the property of the issuing body.

IA CERTIFICATE: MASC S/26-8144X

Equipment: Embedded PC
(Expiry date: 02 April 2029)

Page 2 of 2

ANNEX A

This document is based on and must be read in conjunction with certificate IECEx DEK 17.0020X.	
Description (According to Base Certificate) **	
"Refer to description in Base Certificate ** (and any applicable schedules/issues/variations)."	
Standard compliance	See Base Certificate **
Specific conditions of use ("X")	<p><i>For Ex nA:</i></p> <ul style="list-style-type: none">The equipment shall only be used in an area of not more than pollution degree 2, as defined in IEC 60664-1.The equipment shall be installed in a suitable enclosure providing a degree of protection of at least IP54 according to IEC 60079-15, taking into account the environmental conditions under which the equipment is used.Provisions shall be made to prevent the rated voltage from being exceeded by transient disturbances of more than 119 V. <p><i>For Ex t:</i></p> <ul style="list-style-type: none">The equipment shall be installed in a suitable enclosure providing a degree of protection of IP54 according to IEC 60079-31 for group IIIA or IIIB and IP6X according to IEC 60079-31 for Group IIIC, taking into account the environmental conditions under which the equipment is used.
Conditions of manufacture	<ul style="list-style-type: none">None.
Conditions of Certification	<ul style="list-style-type: none">This IA Certificate covers all units sold from the date of this document to the expiry date of this certificate.As per ARP 0108: 2018 / NCoP 2398: 2022 (as applicable) a maximum three yearly review is required on this IA Certificate (expiry is determined as per the QAR/QAN/QMS expiry date).The apparatus must be additionally marked with the MASC marking details above.This approval only covers the equipment as certified above and does not include any scheduled additions or variations / amendments / new issues to the certificate(s), made after the above date.The equipment does not need to be re-tested when used on the conditions and with such restrictions as prescribed by the certificate on which this IA Certificate is based and any other conditions in this IA Certificate.The certification on which this IA Certificate is based must remain valid.The extent of the requirements in the ARP 0108:2018 / NCoP 2398: 2022 (as applicable), SANS 10108 and any other applicable regulations on the certification of the equipment must remain unchanged.The Ex-quality assurance notification/report for the equipment must remain valid.
Conclusion:	<ul style="list-style-type: none">From the above and the selective examination of the documentation, nothing contrary to the requirements of the applicable standards was found, provided that the equipment / component is used as described in the above document / certificate and according to the MASC conditions below. A MASC IA certificate is issued based on the work done as per the Base Certificate **.The routine tests for production units according to the Base Certificate ** must be complied with (if applicable).

This document is issued based on Mining And Surface Certification's Standard Contract terms and conditions available on request.

While every endeavour is made to ensure that a test / assessment / inspection is representative and accurately performed, and that a report / certificate is accurate in the quoted results and conclusions drawn from the test / assessment / inspection, MASC or its directors/employees shall in no way be liable for any error made in carrying out the test / assessment or for any erroneous statement, whether in fact or in opinion, contained in a report / certificate issued pursuant to a test / assessment / inspection.

MASC takes no responsibility for any non-conformances, exclusions, or any results / assessments / inspections not in compliance with the standards. By marking the equipment in accordance with the documentation / standard, the manufacturer / applicant attests on his own responsibility that the equipment / installation has been designed and constructed in accordance with the applicable requirements of the relevant standards and documentation, that the routine verifications / routine tests have been correctly completed and the equipment / installation complies with the documentation and standard(s).

This document is only for use and application in South Africa. It is issued based on National interpretations and accepted practices.

This document may only be reproduced in full.

This certificate is not transferable and remains the property of the issuing body.

This document will not be supported by MASC for certification purposes outside the borders of South Africa.

Mining And Surface Certification (Pty) Ltd Reg No: 2015/021934/07
Directors: Roelof Viljoen & Francois du Toit
Unit #5, Lelyta Park, 45 Jurg Avenue, Hennospark Ext 87, Centurion, 0157
P.O. Box 14344, Clubview, 0014
Tel: 012 653 2959 ♦ Fax: 086 605 8568
e-mail: info@masc-ex.co.za



IECEX Certificate of Conformity

INTERNATIONAL ELECTROTECHNICAL COMMISSION IEC Certification System for Explosive Atmospheres

for rules and details of the IECEx Scheme visit www.iecex.com

Certificate No.: **IECEX DEK 17.0020X** Page 1 of 3 [Certificate history:](#)

Status: **Current** Issue No: 0

Date of Issue: 2017-05-08

Applicant: **Beckhoff Automation GmbH & Co. KG**
Hülsthorstweg 20
33415 Verl
Germany

Equipment: **Embedded PC Series CX8000**

Optional accessory:

Type of Protection: **Ex nA and Ex tc**

Marking: Ex nA IIC T4 Gc and
Ex tc IIIC T135 °C Dc

Approved for issue on behalf of the IECEx
Certification Body:

R. Schuller

Position:

Certification Manager

Signature:
(for printed version)

Date:
(for printed version)

1. This certificate and schedule may only be reproduced in full.
2. This certificate is not transferable and remains the property of the issuing body.
3. The Status and authenticity of this certificate may be verified by visiting www.iecex.com or use of this QR Code.



Certificate issued by:

DEKRA Certification B.V.
Meander 1051
6825 MJ Arnhem
Netherlands





IECEx Certificate of Conformity

Certificate No.: **IECEx DEK 17.0020X**

Page 2 of 3

Date of issue: 2017-05-08

Issue No: 0

Manufacturer: **Beckhoff Automation GmbH & Co. KG**
Hülsthorstweg 20
33415 Verl
Germany

Manufacturing
locations:

This certificate is issued as verification that a sample(s), representative of production, was assessed and tested and found to comply with the IEC Standard list below and that the manufacturer's quality system, relating to the Ex products covered by this certificate, was assessed and found to comply with the IECEx Quality system requirements. This certificate is granted subject to the conditions as set out in IECEx Scheme Rules, IECEx 02 and Operational Documents as amended

STANDARDS :

The equipment and any acceptable variations to it specified in the schedule of this certificate and the identified documents, was found to comply with the following standards

[IEC 60079-0:2011](#) Explosive atmospheres - Part 0: General requirements
Edition:6.0

[IEC 60079-15:2010](#) Explosive atmospheres - Part 15: Equipment protection by type of protection "n"
Edition:4

[IEC 60079-31:2013](#) Explosive atmospheres - Part 31: Equipment dust ignition protection by enclosure "t"
Edition:2

This Certificate **does not** indicate compliance with safety and performance requirements other than those expressly included in the Standards listed above.

TEST & ASSESSMENT REPORTS:

A sample(s) of the equipment listed has successfully met the examination and test requirements as recorded in:

Test Report:

[NL/DEK/ExTR16.0047/01](#)

Quality Assessment Report:

[DE/BVS/QAR16.0010/00](#)



IECEx Certificate of Conformity

Certificate No.: **IECEx DEK 17.0020X**

Page 3 of 3

Date of issue: 2017-05-08

Issue No: 0

EQUIPMENT:

Equipment and systems covered by this Certificate are as follows:

Embedded PC Series CX8000 for use in I/O and Fieldbus systems.

The type code, the ambient temperature range and the temperature class of the modules shall be taken from Table 1, see Annex.

Electrical data

The electrical data of the supply and the input and output circuits shall be taken from Table 1, see Annex.

SPECIFIC CONDITIONS OF USE: YES as shown below:

For Ex nA:

The equipment shall only be used in an area of not more than pollution degree 2, as defined in IEC 60664-1.

The equipment shall be installed in a suitable enclosure providing a degree of protection of at least IP54 according to IEC 60079-15, taking into account the environmental conditions under which the equipment is used.

Provisions shall be made to prevent the rated voltage from being exceeded by transient disturbances of more than 119 V.

For Ex t:

The equipment shall be installed in a suitable enclosure providing a degree of protection of IP54 according to IEC 60079-31 for group IIIA or IIIB and IP6X according to IEC 60079-31 for Group IIIC, taking into account the environmental conditions under which the equipment is used.

Annex:

[DEK 17.0020X - issue 0 - ExTR16.0047-01.pdf](#)

**Annex 1 to Certificate of Conformity IECEx DEK 17.0020X, issue 0 /
Testreport NL/DEK/ExTR16.0047/01**

Table 1

Description	Type/Beckhoff.	Temp. code	Ambient Range	Technical Data	Supply Volt.
CX8010 Embedded PC for EtherCAT (slave)	CX8010	T4	-25...+60°C	----	24Vdc
CX-Ethernet CPU 400MHz 64MB RAM SUSV	CX8000.5-V1	T4	-25...+60°C	----	----
CX Ethernet Interface 3xRJ45, 1xDIP	CX8095.1-V2	T4	-25...+60°C	----	----
E-/K-Bus Verbinder	CX8003_1	T4	-25...+60°C	----	----
Netzteil Starter-Klemme CX8000	CX5125.7-V2	T4	-25...+60°C	----	24Vdc
CX8030 Embedded PC for EtherCAT (slave)	CX8030	T4	-25...+60°C	----	24Vdc
CX-PB/CAN/DN CPU 400MHz 64MB RAM SUSV	CX8000.5-V3	T4	-25...+60°C	----	----
CX PROFIBUS Interface	CX8031.2-V2	T4	-25...+60°C	----	----
E-/K-Bus Verbinder	CX8003_1	T4	-25...+60°C	----	----
Netzteil Starter-Klemme CX8000	CX5125.7-V2	T4	-25...+60°C	----	24Vdc
CX8031 Embedded PC for PROFIBUS-DP (slave)	CX8031	T4	-25...+60°C	----	24Vdc
CX-PB/CAN/DN CPU 400MHz 64MB RAM SUSV	CX8000.5-V3	T4	-25...+60°C	----	----
CX PROFIBUS Interface	CX8031.2-V2	T4	-25...+60°C	----	----
E-/K-Bus Verbinder	CX8003_1	T4	-25...+60°C	----	----
Netzteil Starter-Klemme CX8000	CX5125.7-V2	T4	-25...+60°C	----	24Vdc
CX8051 Embedded PC for CANopen (slave)	CX8050	T4	-25...+60°C	----	24Vdc
CX-PB/CAN/DN CPU 400MHz 64MB RAM SUSV	CX8000.5-V3	T4	-25...+60°C	----	----
CX CANopen Interface D-Sub S9	CX8051.0-V2	T4	-25...+60°C	----	----
E-/K-Bus Verbinder	CX8003_1	T4	-25...+60°C	----	----
Netzteil Starter-Klemme CX8000	CX5125.7-V2	T4	-25...+60°C	----	24Vdc
CX8051 Embedded PC for CANopen (slave)	CX8051	T4	-25...+60°C	----	24Vdc
CX-PB/CAN/DN CPU 400MHz 64MB RAM SUSV	CX8000.5-V3	T4	-25...+60°C	----	----
CX CANopen Interface D-Sub S9	CX8051.0-V2	T4	-25...+60°C	----	----
E-/K-Bus Verbinder	CX8003_1	T4	-25...+60°C	----	----
Netzteil Starter-Klemme CX8000	CX5125.7-V2	T4	-25...+60°C	----	24Vdc
CX8080 Embedded PC for RS232/RS485	CX8080	T4	-25...+60°C	----	24Vdc
CX-PB/CAN/DN CPU 400MHz 64MB RAM SUSV	CX8000.5-V3	T4	-25...+60°C	----	----
RS232/RS485 Interface EK/CX8000	CX8080.1	T4	-25...+60°C	----	----
E-/K-Bus Verbinder	CX8003_1	T4	-25...+60°C	----	----
Netzteil Starter-Klemme CX8000	CX5125.7-V2	T4	-25...+60°C	----	24Vdc
CX8090 Embedded PC for Ethernet	CX8090	T4	-25...+60°C	----	24Vdc
CX-PB/CAN/DN CPU 400MHz 64MB RAM SUSV	CX8000.5-V3	T4	-25...+60°C	----	----
CX Ethernet Interface 3xRJ45, 1xDIP	CX8031.2-V2	T4	-25...+60°C	----	----
E-/K-Bus Verbinder	CX8003_1	T4	-25...+60°C	----	----
Netzteil Starter-Klemme CX8000	CX5125.7-V2	T4	-25...+60°C	----	24Vdc
CX8091 BACnet/IP and OPC UA	CX8091	T4	-25...+60°C	----	24Vdc
CX-Ethernet CPU 400MHz 64MB RAM SUSV	CX8000.5-V1	T4	-25...+60°C	----	----
CX Ethernet Interface 3xRJ45, 1xDIP	CX8095.1-V2	T4	-25...+60°C	----	----
E-/K-Bus Verbinder	CX8003_1	T4	-25...+60°C	----	----
Netzteil Starter-Klemme CX8000	CX5125.7-V2	T4	-25...+60°C	----	24Vdc

**Annex 1 to Certificate of Conformity IECEx DEK 17.0020X, issue 0 /
Testreport NL/DEK/ExTR16.0047/01**

CX8093 Embedded PC for PROFINET RT (device)	CX8093	T4	-25...+60°C	---	24Vdc
CX-Ethernet CPU 400MHz 64MB RAM SUSV	CX8000.5-V1	T4	-25...+60°C	---	---
CX Ethernet Interface 3xRJ45, 1xDIP	CX8095.1-V2	T4	-25...+60°C	---	---
E-/K-Bus Verbinder	CX8003_1	T4	-25...+60°C	---	---
Netzteil Starter-Klemme CX8000	CX5125.7-V2	T4	-25...+60°C	---	24Vdc
CX8095 Embedded PC for EtherNet/IP (slave)	CX8095	T4	-25...+60°C	---	24Vdc
CX-Ethernet CPU 400MHz 64MB RAM SUSV	CX8000.5-V1	T4	-25...+60°C	---	---
CX Ethernet Interface 3xRJ45, 1xDIP	CX8095.1-V2	T4	-25...+60°C	---	---
E-/K-Bus Verbinder	CX8003_1	T4	-25...+60°C	---	---
Netzteil Starter-Klemme CX8000	CX5125.7-V2	T4	-25...+60°C	---	24Vdc
CX8097 Embedded PC for Sercos III	CX8097	T4	-25...+60°C	---	24Vdc
CX-Ethernet CPU 400MHz 64MB RAM SUSV	CX8000.5-V1	T4	-25...+60°C	---	---
CX Ethernet Interface 3xRJ45, 1xDIP	CX8095.1-V2	T4	-25...+60°C	---	---
E-/K-Bus Verbinder	CX8003_1	T4	-25...+60°C	---	---
Netzteil Starter-Klemme CX8000	CX5125.7-V2	T4	-25...+60°C	---	24Vdc