

ZK1090-0132-0xxx | EtherCAT cable, PUR, AWG26, drag-chain suitable



M8, plug, straight, male, 4-pin, EtherCAT P-coded – M8, socket, straight, female, 4-pin, A-coded – open end, 4-wire + strand and shielding



Plugs

Electrical data	Head A	Head B	Head C
Rated voltage	24 V DC (according to IEC 61076-2-104)	50 V AC/60 V DC (according to IEC 61076-2-104)	-
Rated current	3 A at 40°C (according to IEC 61076-2-104)	4 A at 40°C (according to IEC 61076-2-104)	-
Shielding	yes	yes	-
Insulation resistance	≥ 100 MΩ (according to IEC 60512)	≥ 100 MΩ (according to IEC 60512)	-
Mechanical data			
Accessories type	Connectors	-	-
Installation size	M8	M8	open end
Connector type	plug	socket	-
Configuration	straight	straight	-
Contact type	male	female	-

Number of positions (face)	4-pin	4-pin	4-wire + strand and shielding
Coding	EtherCAT P-coded	A-coded	-
Wire termination	screw connection	-	-
Recommended torque, nut	0.4...0.5 Nm	0.4 Nm	-
Mating cycles	≥ 100	≥ 100	-
Way of locking	screw	screw	-
Weight	0.028 kg (0.0617 lb)	0.028 kg (0.0617 lb)	-
Body color	metal	black	-
Body material	CuZn, Ni	TPU, UL94	-
Coupling nut material	CuZn, Ni	CuZn, Ni	-
Seal	EPDM	FPM	-
O-ring	EPDM	-	-
Contact carrier color	red	green	-
Contact carrier material	PA66 UL94 V0	PA 6, UL 94 V0	-
Contact plating	Au over Ni	Ni, Au gal.	-
Contact material	nickel/gold plated	CuZn	-
Max. wire cross-section	AWG20 (0.5 mm ²)	-	-
Max. cable outer diameter	4.9...6.5 mm	-	-
Environmental data			
Special features	RoHS compliant and lead-free	-	-
UV resistance	yes	-	-
RoHS compliant	yes	yes	-
Ambient temperature (operation)	-40...+85°C, -40...+185°F	-30...+85°C, -22...+185°F	-
Protection rating	IP67 in screwed condition (according to IEC 60529)	IP65/67 in screwed condition (according to IEC 60529)	-
Pollution level	3	3/2 (according to IEC 60664-1)	-
UL	yes, UL E-file number: E480185	-	-

Cable

Electrical data	
Rated voltage	30 V (according to IEC 61076-2-101)
Attenuation of shielding	≥ 43 dB
Insulation resistance	≥ 150 MΩ/km

Unbalanced capacitance to ground	3400 pF/km
Mutual capacitance	51 pF/m at 1 kHz
Characteristic impedance (Ethernet)	100 Ω $\pm$ 15 Ω (100 MHz)
Loop resistance (Ethernet)	250 Ω /km
Unbalanced resistance (Ethernet)	2 %
Dielectric strength wire/wire (Ethernet)	1000 V DC/700 V AC
Dielectric strength wire/shield (Ethernet)	1000 V DC/700 V AC
Signal running time (Ethernet)	5.55 ns/m
Electrical parameters (Ethernet)	based on Cat.5
Test voltage	700 V
Mechanical data	
Cable structure (Ethernet)	star quad
Conductor construction (Ethernet)	19 x 0.1 mm
Cross-section (Ethernet)	1 x 4 x 0.14 mm ² (AWG26)
Outer cable diameter	5.4 mm $\pm$ 0.3 mm (0.213" $\pm$ 0.0118")
Min. bending radius, moved	20 x outer cable diameter
Min. bending radius, fixed installation	4 x outer cable diameter
Weight	40 kg/km (26.9 lb/1000 ft)
Conductor material (Ethernet)	tinned copper
Shielding	braiding of tinned copper wires
Optical covering factor of shielding (Ethernet)	90 %
Use	drag-chain suitable
Max. acceleration	10 m/s ²
Max. speed	15 m/s
Max. number of cycles	20 million (5 million with 14 x D, v = 5 m/s and a = 15 m/s ² , min. 1 million with 9.5 x D, a = 1 m/s ² , travel distance = 1 m)
Wall thickness of wire insulation (Ethernet)	0.25 mm
Jacket color	green
Material jacket	PUR (polyurethane)
Wire color code	yellow, orange, white, blue
Wire insulation material	PP (polypropylene)
Printing on the jacket	"sequential length in meters" Industrial Ethernet Cat5 trailing * E130266 "UL Recognized" UL AWM 20963 80 °C 30V * ZB9032 "month/year" " internal order number"
Printing color	black
Environmental data	
Operation temperature range, moved	-40...+80°C, -40...+176°F

Oil resistance	according to DIN EN 60811-404 (7x24 h/90 °C)
Acid, lye and solvent resistance	depends on medium, concentration, temperature and duration
Flame-retardant	according to AWM Style 20963
CFC-free	yes
Halogen-free	according to IEC 60754-1 and -3
Silicone-free	yes
RoHS compliant	yes
CE	yes
UL	yes, UL E-file number: E130266
Approvals	UL-Style AWM 20963

Attenuation


Max. insertion loss

Frequency [MHz]	1	4	10	16	20	31.25	62.5	100
[db/100 m]	3.1	6.5	9.9	12.3	13.8	17.7	25.6	33.0
[db/100 ft]	0.9	2	3	3.7	4.2	5.4	7.8	10.1


Min. near-end crosstalk attenuation

Frequency [MHz]	1	4	10	16	20	31.25	62.5	100
[db/100 m]	62	53.0	47.0	44.0	42.0	40.0	35.0	32.0
[db/100 ft]	18.9	16.2	14.3	13.4	12.8	12.2	10.7	9.8

Pin assignment



Dimensions



A1	48.5 mm
A2	14.0 mm

B1	40.00 mm
B2	Ø 10.1 mm

Notes

- Depending on the cable length (L), the following length tolerances apply:
0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: + 40 mm | ≥ 4.0 m: + 1%
- Illustrations similar
- Further cable length on request.

Ordering information	Length
ZK1090-0132-0005	0.50 m

Further length on request

Accessories	
ZB8801-0000	torque wrench for hexagonal plugs, adjustable
ZB8801-0001	torque cable key, M8/wrench size 9, for ZB8801-0000
ZB8803-0001	Flange/Panel feed-through for M8 pre-assembled, for fixing the connector, plastic, including screws, washers and lock nuts



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, ATRO®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, MX-System®, Safety over EtherCAT®, TC/BSD®, TwinCAT®, TwinCAT/BSD®, TwinSAFE®, XFC®, XPlanar® and XTS® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 06/2026

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.