



ZK1090-3191-Exxx | EtherCAT cable, PVC, AWG22, fixed installation, CMG, CSA, PLTC



M8, plug, straight, male, 4-pin, A-coded – RJ45, plug, straight, male, 4-pin



Plugs

Electrical data	Head A	Head B
Rated voltage	63 V (according to IEC 61076-2-111)	150 V
Rated current	4 A at 40°C (according to IEC 61076-2-104)	1.5 A
Shielding	yes	yes
Insulation resistance	≥ 100 GΩ (according to IEC 60512)	≥ 10 GΩ (according to IEC 60512-2)
Mechanical data		
Installation size	M8	RJ45
Connector type	plug	plug
Configuration	straight	straight
Contact type	male	male
Number of positions (face)	4-pin	4-pin
Coding	A-coded	-
Recommended torque, nut	0.4 Nm	-
Mating cycles	≥ 100	≥ 750
Way of locking	screw	-

Weight per piece	0.028 kg (0.0617 lb)	-
Body color	black	black
Body material	TPU, UL94	TPU, UL 94 HB
Coupling nut material	GD-Zn, Ni	-
Seal	FPM	-
Contact carrier color	green	-
Contact carrier material	PA 6, UL 94 V0	PC UL 94 V-0
Contact plating	Ni, Au gal.	Ni, Au gal.
Contact material	CuZn	CuZn
Environmental data		
Special features	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1	-
RoHS compliant	yes	yes
Ambient temperature (operation)	-30...+70°C, -22...+158°F	-40...+70°C, -40...+158°F
Protection rating	IP65/67 in screwed condition (according to IEC 60529)	IP20
Pollution level	3/2 (according to IEC 60664-1)	-

Cable


Electrical data		
Rated voltage	600 V	
Operating voltage	≤ 125 V (peak value, not for high voltage purposes)	
Insulation resistance	≥ 0.5 GΩ/km	
Mutual capacitance	48 nF/km	
Wire resistance (Ethernet)	≤ 58.0 Ω/km (20°C)	
Characteristic impedance (Ethernet)	100 Ω ±15 Ω (100 MHz)	
Signal running time (Ethernet)	5.3 ns/m	
Electrical parameters (Ethernet)	based on Cat.5	
Test voltage	≥ 2000 V	
Mechanical data		
Cable structure (Ethernet)	twisted shielded pair	
Conductor construction (Ethernet)	7-strand	
Cross-section (Ethernet)	2 x 2 x 0.34 mm ² (AWG22)	
Outer cable diameter	6.5 mm ± 0.2 mm (0.2559" ± 0.0079")	
Min. bending radius, moved	10 x outer cable diameter	
Min. bending radius, fixed installation	5 x outer cable diameter	

Weight	67 kg/km (45.0 lb/1000 ft)
Shielding	braiding of tinned copper wires
Optical covering factor of shielding (Ethernet)	90 %
Use	fixed installation
Jacket color	green
Material jacket	PVC (polyvinyl chloride)
Wire color code	yellow, orange, white, blue
Printing color	black
Environmental data	
Operation temperature range, moved	-20...+60°C, -4...+140°F
Operation temperature range, fixed installation	-40...+80°C, -40...+176°F
Flame-retardant	according to DIN VDE 0482-332-3 / DIN EN 60332-3 / IEC60332-3
Approvals	CMG, CSA, PLTC

Attenuation								
Max. insertion loss								
Frequency [MHz]	1	4	10	16	20	31.25	62.5	100
[db/100 m]	1.6	3.2	5.2	6.9	7.8	10.5	15.0	19.5
[db/100 ft]	0.5	1	1.6	2.1	2.4	3.2	4.6	5.9
Min. near-end crosstalk attenuation								
Frequency [MHz]	1	4	10	16	20	31.25	62.5	100
[db/100 m]	80	75.0	70.0	65.0	63.0	60.0	55.0	50.0
[db/100 ft]	24.4	22.9	21.3	19.8	19.2	18.3	16.8	15.2

Contact assembly	
<p>The diagram illustrates the contact assembly for an 8-pin connector. It shows two rows of 4 pins each, numbered 1 to 8. The top row (pins 1-4) is connected to the bottom row (pins 1-4) in a 1:1 configuration. Additionally, the top row (pins 1-4) is connected to the bottom row (pins 5-8) in a 1:1 configuration. The wire colors are labeled as follows: gelb/yellow (top 1 to bottom 1 and bottom 5), weiß/white (top 2 to bottom 2 and bottom 6), orange (top 3 to bottom 3 and bottom 7), and blau/blue (top 4 to bottom 4 and bottom 8).</p>	

Dimensions



A1	41.00 mm
A2	Ø 10.1 mm
B1	43.80 mm

Notes

- Depending on the cable length (L), the following length tolerances apply:
0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: + 40 mm | ≥ 4.0 m: + 1%
- Illustrations similar
- Further cable length on request.

Ordering information

Length

ZK1090-3191-E020	2.00 m
------------------	--------

Further length on request

Accessories

ZB8801-0000	torque wrench for hexagonal plugs, adjustable
ZB8801-0001	torque cable key, M8/wrench size 9, for ZB8801-0000
ZB8803-0001	Flange/Panel feed-through for M8 pre-assembled, for fixing the connector, plastic, including screws, washers and lock nuts
ZK1096-9696-0000	RJ45, socket, straight, female, 8-pin – RJ45, socket, straight, female, 8-pin



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2025

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.