


ZK1090-6162-6xxx | EtherCAT cable, PUR, AWG22, capable of torsion



M12, plug, straight, male, 4-pin, D-coded – M12, socket, straight, female, 4-pin, D-coded



Plugs

Electrical data	Head A	Head B
Rated voltage	160 V (according to IEC 61076-2-101)	160 V (according to IEC 61076-2-101)
Rated current	4 A at 40°C (according to IEC 61076-2-101)	4 A at 40°C (according to IEC 61076-2-101)
Rated impulse voltage	2.5 kV	2.5 kV
Shielding	yes	yes
Contact resistance	< 5 mΩ	< 5 mΩ
Insulation resistance	≥ 10 GΩ (according to IEC 60512-2)	≥ 10 GΩ (according to IEC 60512-2)
Mechanical data		
Installation size	M12	M12
Connector type	plug	socket
Configuration	straight	straight
Contact type	male	female
Number of positions (face)	4-pin	4-pin
Coding	D-coded	D-coded

Recommended torque, nut	0.6 Nm	0.6 Nm
Mating cycles	≥ 100 (according to IEC 60512-9a)	≥ 100 (according to IEC 60512-9a)
Way of locking	screw	screw
Body color	black	black
Body material	TPU, UL 94	TPU, UL 94
Coupling nut material	CuZn, Ni	CuZn, Ni
Seal	FPM	FPM
Contact carrier color	green	green
Contact carrier material	TPU GF, UL 94	TPU GF, UL 94
Contact plating	Ni, Au gal.	Ni, Au gal.
Contact material	CuZn	CuZn
Environmental data		
UV resistance	yes	-
RoHS compliant	yes	yes
Ambient temperature (operation)	-30...+80°C, -22...+176°F	-30...+80°C, -22...+176°F
Protection rating	IP65/67 in screwed condition (according to IEC 60529)	IP65/67 in screwed condition (according to IEC 60529)
Pollution level	3/2 (according to IEC 60664-1)	3/2 (according to IEC 60664-1)
Approvals	UL, CSA	-

Cable


Electrical data	
Rated voltage	600 V
Insulation resistance	≥ 5GΩ * km
Mutual capacitance	48 nF/km
Characteristic impedance (Ethernet)	100 Ω ±15 Ω
Loop resistance (Ethernet)	≤ 115 Ω/km
Signal running time (Ethernet)	5.3 ns/m
Electrical parameters (Ethernet)	based on Cat.5
Test voltage	1500 V, 50 Hz, 1 min.
Mechanical data	
Cable structure (Ethernet)	star quad
Conductor construction (Ethernet)	19-strand
Cross-section (Ethernet)	1 x 4 x 0.34 mm ² (AWG22)
Outer cable diameter	6.6 mm ± 0.2mm (0.259" ± 0.0079")
Min. bending radius, moved	10 x outer cable diameter

Min. bending radius, fixed installation	5 x outer cable diameter
Conductor material (Ethernet)	tinned copper
Shielding	two layers of conductive wrapping and braiding of special wires
Optical covering factor of shielding (Ethernet)	≥ 85 %
Use	suitable for torsion/robotic applications
Max. acceleration	20 m/s ²
Max. speed	4 m/s
Max. travel distance	5 m
Max. number of cycles	1 million
Jacket color	green
Material jacket	PUR (polyurethane)
Material jacket, further characteristics of	halogen-free, flame-retardant, matt and low adhesion
Wire color code	yellow, orange, white, blue
Wire insulation material	PO (Polyolefine)
Printing on the jacket	XXX Beckhoff Automation GmbH & Co. KG-Germany-ZB9021 EtherCAT Cat5e Torsion AWG22/19 E170315 cRUus> AWM21209 AWM I/II A/B 90°C 600V MM/YY CE
Printing color	black
Torsion angle in °/m	max. ± 180°/m
Torsion speed	36 cycle/min.
Number of torsion cycles	5 million
Load weight	20 N
Claimed torsion length	1 m
Environmental data	
Operation temperature range, moved	-30...+90°C, -22...+194°F
Operation temperature range, fixed installation	-40...+90°C, -40...+194°F
Oil resistance	according to DIN EN 60811-404 (7x24 h/90 °C)
Flame-retardant	VW-1 Flame Test UL 1581 section 1080 and IEC 60332-1-2
Halogen-free	according to IEC 60754 or DIN VDE 0472 part 815
UL	yes, UL E-file number: E170315


Attenuation								
Max. insertion loss								
Frequency [MHz]	1	4	10	16	20	31.25	62.5	100
[db/100 m]	-	4.9	7.8	9.9	11.1	14.1	62.5	26.4
[db/100 ft]	-	1.5	2.4	3	3.4	4.3	19.1	8
Min. near-end crosstalk attenuation								

Frequency [MHz]	1	4	10	16	20	31.25	62.5	100
[db/100 m]	-	56.3	50.3	47.2	45.8	42.9	38.4	35.3
[db/100 ft]	-	17.2	15.3	14.4	14	13.1	11.7	10.8

Pin assignment



Dimensions



A1	49.00 mm
A2	Ø14.50 mm
B1	43.00 mm
B2	M16

Notes

- Depending on the cable length (L), the following length tolerances apply:
0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: $+ 40$ mm | ≥ 4.0 m: $+ 1\%$
- Illustrations similar
- Further cable length on request.

CE, UL

CE	yes
----	-----

Ordering information

Length

ZK1090-6162-6050	5.00 m
------------------	--------

Further length on request

Accessories

ZB8801-0000	torque wrench for hexagonal plugs, adjustable
ZB8801-0002	torque cable key, M12/wrench size 13, for ZB8801-0000



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, ATRO®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, MX-System®, Safety over EtherCAT®, TC/BSD®, TwinCAT®, TwinCAT/BSD®, TwinSAFE®, XFC®, XPlanar® and XTS® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 07/2026

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.