


ZK2000-6200-7xxx | Sensor cable, PP, 4 x 0.25 mm², fixed installation, food & beverage



M12, socket, straight, female, 4-pin, A-coded – open end, 4-wire



Plugs



Electrical data	Head A	Head B
Rated voltage	250 V (according to IEC 61076-2-101)	-
Rated current	4 A at 40°C (according to IEC 61076-2-101)	-
Shielding	no	-
Insulation resistance	≥ 10 GΩ (according to IEC 60512-2)	-
Mechanical data		
Installation size	M12	open end
Connector type	socket	-
Configuration	straight	-
Contact type	female	-
Number of positions (face)	4-pin	4-wire
Coding	A-coded	-
Recommended torque, nut	0.6 Nm	-
Mating cycles	≥ 100 (according to IEC 60512-9a)	-
Way of locking	screw	-

Body color	black	-
Body material	thermoplastic elastomer	-
Coupling nut material	1.4404 (stainless steel)	-
Seal	FPM	-
Contact carrier color	red	-
Contact carrier material	PP GF, UL94	-
Contact plating	Ni, Au gal.	-
Contact material	CuZn	-
Environmental data		
RoHS compliant	yes	-
Ambient temperature (operation)	-30...+105°C, -22...+221°F	-
Protection rating	IP65/67 in screwed condition (according to IEC 60529)	-
Pollution level	3/2 (according to IEC 60664-1)	-

Cable

Electrical data		
Rated voltage	250 V	
Operating voltage	≤ 250 V	
Insulation resistance	≥ 10 GΩ * km	
Test voltage	2000 V, 50 Hz, 5 min	
Mechanical data		
Conductor construction (power)	42 x 0.10 mm	
Cross-section (power)	4 x 0.34 mm ² (AWG22)	
Min. bending radius, moved	8 x outer cable diameter	
Min. bending radius, fixed installation	5 x outer cable diameter	
Weight	30.45 kg/km (20.5 lb/1000 ft)	
Conductor material (power)	copper bare	
Shielding	no	
Use	Food and Beverage	
Max. number of cycles	20 million	
Wall thickness of wire insulation (signal/24V)	0.15 mm	
Jacket color	orange	
Material jacket	PP (polypropylene)	
Wire color code	white, blue, black, brown	
Wire insulation material	TPE (thermoplastic elastomer)	

Printing color	black
Environmental data	
Operation temperature range, moved	-40...+105°C, -40...+221°F
Operation temperature range, fixed installation	-50...+105°C, -58...+221°F
Flame-retardant	according to DIN VDE 0472, part 804, type of test B

Contact assembly**Dimensions**

A1	43.80 mm
----	----------

Notes

- Depending on the cable length (L), the following length tolerances apply:
0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: + 40 mm | ≥ 4.0 m: + 1%
- Illustrations similar
- Further cable length on request.

Ordering information	Length
ZK2000-6200-7010	1.00 m

Accessories

ZB8801-0000	torque wrench for hexagonal plugs, adjustable
ZB8801-0002	torque cable key, M12/wrench size 13, for ZB8801-0000



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 08/2024

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.