


# ZK4875-9006-xxxx | DC link connection cable 6 mm<sup>2</sup>, static use



AX-Bridge, straight, male, Power: 2+PE – open end, 2-wire




## Plugs

Electrical data	Head A	Head B
Rated voltage	680 V DC	-
Rated current (power)	50 A DC	-
Mechanical data		
Installation size	AX-Bridge	open end
Configuration	straight	-
Contact type	male	-
Number of positions (face)	Power: 2+PE	2-wire
Mating cycles	25	-
Way of locking	AX-Bridge	-
Body color	white	-
Body material	plastics	-
Environmental data		
Ambient temperature (operation)	+5...+40°C, +41...+104°F	-
Protection rating	IP20	-

## Cable

Electrical data	
Operating voltage	300/500 V (according to DIN VDE 0298-3)
Insulation resistance	$\geq 20 \text{ M}\Omega \cdot \text{km}$
Test voltage	$\geq 6000 \text{ V}$
Mechanical data	
Cross-section (power)	2 x 6 mm <sup>2</sup> (approx. AWG10)
Min. bending radius, moved	15 x outer cable diameter
Min. bending radius, fixed installation	4 x outer cable diameter
Conductor material	copper bare
Use	fixed installation
Jacket color	gray
Material jacket	PVC (polyvinyl chloride)
Wire color code	black with white numbers
Wire insulation material	PVC (polyvinyl chloride)
Printing color	black
Environmental data	
Operation temperature range, moved	-5...+90°C, 23...+194°F
Operation temperature range, fixed installation	-40...+90°C, -40...+194°F
Oil resistance	yes
Acid, lye and solvent resistance	good resistance to acids, alkalis and solvents
LABS-free	yes
Halogen-free	no
Silicone-free	yes
UL	yes

## Dimensions



A1	190.00 mm
A2	80.00 mm
A3	40.00 mm
A4	5.60 mm

## Notes

- Depending on the cable length (L), the following length tolerances apply:  $\pm 2\text{-}3\%$
- Illustrations similar
- The last three digits of the ordering information is the cable length in decimeters, e.g. ZK4xxx-xxxx-x020 = cable length 2.00 m

Ordering information	Length
ZK4875-9006-xxxx	xxxx = cable length in decimeters
xxxx = 0050	example for 5 m length
	sold by the meter, admissible total cable length see documentation of Servo Drive



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 12/2024

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.