


# ZS7200-0009 | Plug, field assembly, EtherCAT P, IP65/67, shielded




B17, socket, straight, male+male, pins 3+4, P-coded



Electrical data	
Shielding	yes
Mechanical data	
Installation size	B17
Connector type	socket
Configuration	straight
Contact type	male+male
Number of positions (face)	pins 3+4
Coding	P-coded
Wire termination	crimp connection
Max. wire cross-section (power)	AWG16/1.5 mm <sup>2</sup>
Max. wire cross-section (Ethernet)	AWG22/0.34 mm <sup>2</sup>
Environmental data	

Dimensions	
------------	--



### Ordering information

ZS7200-0009

B17, socket, metal, shielded, crimp, straight, male+male, 3+4-pin, P-coded, IP65/67, Ø 10.0...11.5 mm



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 08/2024

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.