




Assembly instruction B17 hybrid

field attachable flange housing with crimp connection, axial.
3x1.5mm² + 4xAWG22, ENP: power (female) / data (male)

parts list



Flange type depends on product number!

ZS7200-Z005

ZS7200-Zxxx


ZS7200-Zxxx

ZS7200-Zxxx





ZS7200-Zxxx

ZS7200-Zxxx






Component only installed in ZS7200-Zxxx.



Components only installed in ZS7200-Zxxx.



Stick the copper band around the shielding braid. Shielding braid must not protrude beyond the copper band.



width across flats 30

fig. similar

Color marking optional!



Lock retaining ring in the groove!

Centering ring is used only in ZS7200-Zxxx, flat seal is used in ZS7200-Zxxx and ZS7200-Zxxx!

Please consider the cable direction!
Attention: View from mating side!



Attention: View from cable outlet!
Consider the right choice of colors!



tools / accessory parts

crimping tool	crimping insert / locator
ZB8810-0000	ZB8810-0001