

C9900-K184 | TNC plug, coaxial, straight, pin, solder/screw, 50 ohms



TNC plug, plug, straight, male, 1-pin + shield



Electrical data	
Shielding	yes
Contact resistance	< 3 mΩ (inside), < 2 mΩ (outside)
Insulation resistance	≥ 5 GΩ
Mechanical data	
Installation size	TNC plug
Connector type	plug
Configuration	straight
Contact type	male
Number of positions (face)	1-pin + shield
Wire termination	solder connection
Mating cycles	≥ 500
Way of locking	screw
Weight	0.004 kg (0.0088 lb)
Body color	metal
Body material	brass/nickel plated
Seal	silicone

Contact plating	Au
Contact material	brass/gold plated
Max. cable outer diameter	7.3 mm
Environmental data	
Special features	TNC 7, PTFE dielectric, impedance 50 Ohm, max. frequency 4 GHz
Use	for Aircell 7 cable
RoHS compliant	yes
Ambient temperature (operation)	-55...+155°C, -67...+311 °F

Ordering information

C9900-K184	TNC plug, coaxial, straight, pin, solder/screw, 50 ohms
------------	---



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, ATRO®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, MX-System®, Safety over EtherCAT®, TC/BSD®, TwinCAT®, TwinCAT/BSD®, TwinSAFE®, XFC®, XPlanar® and XTS® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 03/2026

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.