

ZK4100-8121-2xxx | Motor connection cable 0.75 mm² with M23 speedtec[®] plug, drag-chain suitable



M23, plug, straight, female, Power: 3+PE, Signal: 5 – ix Industrial[™], plug, straight, male, 10-pin, Type A – Pitch dimension 7.62 mm, plug, straight, female, 6-pin



Plugs

Electrical data	Head A	Head B	Head D
Rated voltage	-	50 V AC/60 V DC	-
Rated voltage (power)	630 V AC/DC	-	600 V (accordig to UL 1059)
Rated voltage (signal/24V)	250 V AC/DC	-	-
Rated current (power)	30 A max.	-	20 A DC
Test voltage	-	500 V	-
Rated current	-	1.5 A	-
Rated current (signal/24V)	7 A max.	-	-
Rated impulse voltage (power)	6.0 kV	-	6.0 kV
Rated impulse voltage (signal/24V)	2.5 kV	-	-
Shielding	-	yes	-

Contact resistance	< 5 mΩ (signal), < 3 mΩ (power)	< 30 mΩ	< 5 mΩ
Insulation resistance	-	≥ 500 MΩ/km	≥ 100 MΩ (according to IEC 60512)
Insulation group	-	-	IIIa
Transmission characteristics	-	Cat.6 Class EA up to 500 MHz, 10/100 Mbit/s, 1/10 Gbit/s	-
Mechanical data			
Accessories type	Connectors	-	Connectors
Installation size	M23	ix Industrial™	Pitch dimension 7.62 mm
Connector type	plug	plug	plug
Configuration	straight	straight	straight
Contact type	female	male	female
Number of positions (face)	Power: 3+PE, Signal: 5	10-pin	6-pin
Coding	-	Type A	-
Wire termination	crimp connection	IDC	Push-in
Recommended torque, screw termination	-	-	0.5...0.6 Nm
Mating cycles	500	≥ 5000	25
Insertion force	-	-	8 N/pol
Way of locking	Speedtec®	push-pull	locking pin
Weight	0.143 kg (0.3153 lb)	-	0.015 kg (0.0322 lb)
Body color	metal	black	black, similar to RAL 9011
Body material	zinc diecast/nickel plated	Polycarbonate resin	-
Seal	FKM	-	-
Clamp ring	brass/nickel plated	-	-
Contact carrier color	-	-	black
Contact carrier material	PA 6.6 mod., UL 94 V-0	-	PBT, UL 94 V-0
Contact plating	-	Au	tinned
Contact material	brass/gold plated	copper alloy	copper alloy
Max. wire cross-section	-	AWG24...AWG22 (0.25mm²...0.34mm²)	AWG20 ... AWG12 (0.5 mm²...2.50 mm²)
Stripping length	-	-	10 mm + 0,5 mm
Max. cable outer diameter	-	6.0...7.2 mm	-
Environmental data			
Special features	Max. height for operation 2000 m	-	-
RoHS compliant	-	yes	yes


Ambient temperature (operation)	-20...+130°C, -4...+266°F	-	-50...+100°C, -58...+212°F
Protection rating	IP66/67 in screwed condition	IP20	IP20
Pollution level	3 (according to VDE 0110/EN61984 part 6.19.2.2)	-	3
Approvals	-	UL 1977 ECBT2.E102079, CSA-C22.2 No. 182.3 ECBT8.E102079	-
UL	yes, UL E-file number: E247738	yes	yes
Overvoltage category	3 (according to VDE 0110/EN61984 part 6.19.2.2)	-	3

Cable

Electrical data	
Operating voltage	≤ 600 V
Insulation resistance	10 MΩ * km
Characteristic impedance	100 Ω (100 MHz)
Dielectric strength wire/wire	3 kV
Dielectric strength wire/shield	2 kV
Mechanical data	
Cross-section	4 x 0.75 mm ² + 2 x 0.25 mm ² + (2 x AWG24)
Cross-section (power)	0.75 mm ² (approx. AWG18)
Outer cable diameter	9.2 ±0.3 mm
Min. bending radius, moved	6.5 x outer cable diameter
Min. bending radius, fixed installation	5 x outer cable diameter
Conductor material	copper bare
Use	drag-chain suitable
UL-Style	cULus AWM Style 2570 80°C 600V
Max. number of cycles	3 million
Jacket color	orange
Material jacket	PUR (polyurethane)
Wire color code	power: black, brown, gray, green/yellow brake: black, red signal: white, blue
Wire insulation material	TPE (thermoplastic elastomer)
Printing on the jacket	Beckhoff Automation GmbH & Co. KG - D - Verl - 4G0.75 + 2x0.25 + (2xAWG24)/C E63216 (UL) AWM Style 21223 80°C 600V XX/JJ - Desina -
Printing color	black
Environmental data	

Operation temperature range, moved	-20...+80°C, -4...+176°F
Ambient temperature, transport/storage	-40...+80°C, -40...+176°F
Halogen-free	yes
RoHS compliant	yes
UL	yes, UL E-file number: E63216
Approvals	UL-Style AWM 2570 80°C 600V

Pin assignment



Dimensions



A1	79.00 mm
A2	28.00 mm
B1	30.00 mm
B2	17.00 mm

Notes

- Depending on the cable length (L), the following length tolerances apply: $\pm 2\text{-}3\%$
- Illustrations similar
- The last three digits of the ordering information is the cable length in decimeters, e.g. ZK4xxx-xxxx-x020 = cable length 2.00 m

CE, UL	
CE	yes
UL	yes, UL E-file number: E63216

Ordering information	Length
ZK4100-8121-2050	5.00 m



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, ATRO®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, MX-System®, Safety over EtherCAT®, TC/BSD®, TwinCAT®, TwinCAT/BSD®, TwinSAFE®, XFC®, XPlanar® and XTS® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 01/2026

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.