


ZK4530-8110-0xxx | Resolver connection cables 0.25 mm² with itec[®] plug, drag-chain suitable



itec[®] (Series 615), plug, straight, female, 12-pin – D-sub, plug, angled, female, 15-pin



Plugs


Electrical data	Head A	Head B
Rated voltage (signal/24V)	63 V AC/DC	-
Rated current (signal/24V)	5 A max.	-
Rated impulse voltage (signal/24V)	1.5 kV	-
Contact resistance	< 5 mΩ	-
Mechanical data		
Accessories type	Connectors	Connectors
Installation size	itec [®] (Series 615)	D-sub
Connector type	plug	plug
Configuration	straight	angled
Contact type	female	female
Number of positions (face)	12-pin	15-pin
Wire termination	crimp connection	solder connection
Mating cycles	500	-


Way of locking	bayonet	screw
Weight	0.025 kg (0.0551 lb)	0.055 kg (0.1213 lb)
Body color	black, similar to RAL 9011	metal
Body material	zinc diecast/plastic	zinc diecast/nickel plated
Seal	FKM	-
Clamp ring	plastic	-
Contact carrier material	PBT, PA, UL 94 V-0	-
Contact material	brass/gold plated	-
Environmental data		
Special features	Max. height for operation 2000 m	-
Ambient temperature (operation)	-20...+130°C, -4...+266°F	-
Protection rating	IP66/67 in screwed condition	IP20
Pollution level	3 (according to VDE 0110/EN61984 part 6.19.2.2)	-
Overvoltage category	3 (according to VDE 0110/EN61984 part 6.19.2.2)	-

Cable

Electrical data	
Operating voltage	max. 300 V AC (UL), U ₀ /U 300/300 V (VDE)
Insulation resistance	≥ 500 MΩ
Wire resistance	≤ 76.0 Ω/km
Test voltage	1500 V (wire/wire and wire/screen)
Mechanical data	
Cross-section	4 x 2 x 0.25 mm ²
Outer cable diameter	7.5 mm ± 0.3 mm (0.2952" ± 0.0118")
Min. bending radius, moved in drag-chain	10 x outer cable diameter
Min. bending radius, fixed installation	8 x outer cable diameter
Weight	80.3 kg/km (53.954 lb/1000 ft)
Conductor material	copper, tinned
Optical covering factor of shielding	≥ 85%
Use	drag-chain suitable
Max. acceleration	20 m/s ²
Max. speed	3 m/s
Max. travel distance	5 m
Max. number of cycles	5 million

Jacket color	green
Material jacket	PUR (polyurethane)
Wire color code	brown, green, yellow, gray, pink, blue, red, white
Wire insulation material	PP (polypropylene)
Printing color	black
Torsion angle in °/m	max. ± 30 °/m
Max. tensile load, dynamic	20 N/mm ²
Max. tensile load, static	50 N/mm ²
Environmental data	
Operation temperature range, moved	-20...+80°C, -4...+176°F
Operation temperature range, fixed installation	-40...+80°C, -40...+185°F
Oil resistance	according to UL 1581
Flame-retardant	according to IEC 60332-1
CFC-free	yes
Halogen-free	yes
Silicone-free	yes
RoHS compliant	yes
CE	yes
UL	yes, UL E-file number: E356538
Approvals	cRUus AWM Style 20233, CE compliant

Pin assignment**Dimensions**



A1	44.00 mm
A2	19.00 mm
B1	46.00 mm
B2	41.00 mm

Notes

- Depending on the cable length (L), the following length tolerances apply: $\pm 2-3\%$
- Illustrations similar
- The last three digits of the ordering information is the cable length in decimeters, e.g. ZK4xxx-xxxx-x020 = cable length 2.00 m

Ordering information	Length
ZK4530-8110-0010	1.00 m
ZK4530-8110-0020	2.00 m
ZK4530-8110-0030	3.00 m
ZK4530-8110-0040	4.00 m
ZK4530-8110-0050	5.00 m
ZK4530-8110-0052	5.20 m
ZK4530-8110-0054	5.40 m
ZK4530-8110-0060	6.00 m
ZK4530-8110-0070	7.00 m
ZK4530-8110-0080	8.00 m
ZK4530-8110-0090	9.00 m
ZK4530-8110-0100	10.00 m
ZK4530-8110-0110	11.00 m
ZK4530-8110-0120	12.00 m
ZK4530-8110-0130	13.00 m
ZK4530-8110-0140	14.00 m

ZK4530-8110-0150	15.00 m
ZK4530-8110-0160	16.00 m
ZK4530-8110-0170	17.00 m
ZK4530-8110-0180	18.00 m
ZK4530-8110-0190	19.00 m
ZK4530-8110-0200	20.00 m
ZK4530-8110-0220	22.00 m
ZK4530-8110-0230	23.00 m
ZK4530-8110-0250	25.00 m
ZK4530-8110-0260	26.00 m
ZK4530-8110-0300	30.00 m
ZK4530-8110-0350	35.00 m
ZK4530-8110-0500	50.00 m
ZK4530-8110-0550	55.00 m

Beckhoff®, ATRO®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, MX-System®, Safety over EtherCAT®, TC/BSD®, TwinCAT®, TwinCAT/BSD®, TwinSAFE®, XFC®, XPlanar® and XTS® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 10/2025

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.