

ZK4800-8022-0xxx | Motor connection cable 1 mm², drag-chain suitable



itec[®] (Series 915), plug, straight, female, Power: 3+PE, Signal: 5 – Pitch dimension 7.62 mm, plug, 30°, female, 4-pin



Plugs

Electrical data	Head A	Head B
Rated voltage (power)	630 V AC/DC	1000 V AC/DC (according to IEC 60664-1, IEC 61984), 600 V (according to UL 1059)
Rated voltage (signal/24V)	63 V AC/DC	-
Rated current (power)	14 A	34 A at 40°C (according to IEC 60664-1, IEC 61984), 33 A at 40°C (according to UL 1059)
Rated current (signal/24V)	3.6 A	-
Rated impulse voltage (power)	6.0 kV	8.0 kV
Rated impulse voltage (signal/24V)	1.5 kV	-
Contact resistance	< 5 mΩ	4.5 mΩ
Insulation resistance	-	≥ 100 MΩ (according to IEC 60512)
Insulation group	-	II
Mechanical data		
Accessories type	Connectors	Connectors

Installation size	itec® (Series 915)	Pitch dimension 7.62 mm
Connector type	plug	plug
Configuration	straight	30°
Contact type	female	female
Number of positions (face)	Power: 3+PE, Signal: 5	4-pin
Wire termination	crimp connection	Push-in
Mating cycles	500	25
Way of locking	bayonet	flange and screw
Weight	0.035 kg (0.0772 lb)	0.029 kg (0.0640 lb)
Body color	black, similar to RAL 9011	black, similar to RAL 9011
Body material	zinc diecast/plastic	PA GF, UL 94 V-0
Seal	FKM	-
Clamp ring	brass/nickel plated	-
Contact carrier material	PBT, PA, UL 94 V-0	PA GF, UL 94 V-0
Contact material	brass/gold plated	copper alloy
Max. wire cross-section	-	AWG24...AWG8 (0.5 mm ² ...10 mm ²)
Environmental data		
Special features	Max. height for operation 2000 m	-
Shock resistance	30 g (conforms to EN 60060-2-27), 11 ms; 18 shocks per direction, 3 axes	-
Vibration resistance	10 g (conforms to EN 60068-2-27), 50 Hz...2000 Hz; 1 Octave/min.; 10 cycles per axis	-
Ambient temperature (operation)	-20...+130°C, -4...+266°F	-50...+125°C, -58...+257°F
Protection rating	IP66/67 in screwed condition	IP20
Pollution level	3 (according to VDE 0110/EN61984 part 6.19.2.2)	3
UL	yes, UL E-file number: E247738	-
Overvoltage category	3 (according to VDE 0110/EN61984 part 6.19.2.2)	3


Cable

Electrical data		
Operating voltage	max. 1000 V AC (UL), U _o /U 600/1000 V (VDE)	
Insulation resistance	≥ 500 MΩ * km (DIN EN 50395)	
Mutual capacitance	Signal: 45 ± 15 pF/m, Power: 90 pF/m (at 800 Hz according to EN 50289-1-5)	
Wire resistance (power)	≤ 19.5 Ω/km (DIN EN 50395)	
Wire resistance (signal/24V)	≤ 55.0 Ω/km (DIN EN 50395)	


Wire resistance (brake)	≤ 26.0 Ω/km (DIN EN 50395)
Characteristic impedance	Signal: 110 Ω ± 10 Ω (10 MHz) acc. to EN50289-1-11
Dielectric strength wire/wire (power)	4 kV 50 Hz 5 min. (DIN VDE 0472 T.509C)
Dielectric strength wire/shield (power)	4 kV 50 Hz 5 min. (DIN VDE 0472 T.509C)
Dielectric strength wire/wire (signal/24V)	3 kV 50 Hz 1 min. (DIN VDE 0472 T.509C)
Dielectric strength wire/shield (signal/24V)	3 kV 50 Hz 1 min. (DIN VDE 0472 T.509C)
Mechanical data	
Cross-section (power)	1.00 mm ² (approx. AWG18)
Cross-section (signal)	AWG22 (approx. 0.34 mm ²)
Cross-section (brake)	0.75 mm ² (AWG18)
Outer cable diameter	11.6 mm ± 0.4 mm (0.4567" ± 0.0157")
Min. bending radius, moved in drag-chain	7 x outer cable diameter
Min. bending radius, fixed installation	5 x outer cable diameter
Weight	215 kg/km (144.459 lb/1000 ft)
Conductor material	copper bare
Optical covering factor of shielding	≥ 85%
Use	drag-chain suitable
Max. acceleration	30 m/s ² by 5 m travel distance 15 m/s ² by 10 m travel distance 5 m/s ² by 20 m travel distance
Max. speed	4 m/s
Max. travel distance	20 m (horizontal) 5 m (vertical)
Max. number of cycles	5 million
Jacket color	orange
Material jacket	TPU (thermoplastic polyurethane)
Wire insulation material	PP (polypropylene)
Printing on the jacket	Beckhoff Automation GmbH & Co. KG - D - Verl - 4G1 + (2x0.75)/C + (2xAWG22)/C C E170315 cURus AWM Style 21223 AWM I/II A/B 80°C 1000V FT1 MM/JJ - Desina -
Printing color	black
Torsion angle in °/m	max. ± 30 °/m
Max. tensile load, dynamic	20 N/mm ²
Max. tensile load, static	50 N/mm ²
Environmental data	
Operation temperature range, moved	-20...+80°C, -4...+176°F. In drag-chain with mechanical strain: -20...+60°C, -4...+140°F
Operation temperature range, fixed installation	-40...+80°C, -40...+176°F

UV resistance	UV resistance of the outer jacket referred to DIN EN ISO 4892-2
Oil resistance	according to DIN EN 60811-404, HD22.10 appendix A
Flame-retardant	according to IEC 60332-1-2 UL758 cable flame test
CFC-free	yes
Halogen-free	according to DIN VDE 0472 part 815
Silicone-free	yes
RoHS compliant	yes
UL	yes, UL E-file number: E170315
Approvals	UL758 (AWM) Style 21223 (jacket) and Style 10492 (core)

Pin assignment



Dimensions



A1	44.00 mm
A2	19.00 mm
B1	60.00 mm
B2	47.00 mm

Notes

- Depending on the cable length (L), the following length tolerances apply: $\pm 2\%$
- Illustrations similar

- The last three digits of the ordering information is the cable length in decimeters, e.g. ZK4xxx-xxxx-x020 = cable length 2.00 m

Suitable for operation with TwinSAFE SBC/SBT.

Ordering information	Length
ZK4800-8022-0005	0.50 m
ZK4800-8022-0008	0.80 m
ZK4800-8022-0010	1.00 m
ZK4800-8022-0013	1.30 m
ZK4800-8022-0014	1.40 m
ZK4800-8022-0015	1.50 m
ZK4800-8022-0018	1.80 m
ZK4800-8022-0020	2.00 m
ZK4800-8022-0022	2.20 m
ZK4800-8022-0023	2.30 m
ZK4800-8022-0024	2.40 m
ZK4800-8022-0025	2.50 m
ZK4800-8022-0027	2.70 m
ZK4800-8022-0030	3.00 m
ZK4800-8022-0032	3.20 m
ZK4800-8022-0033	3.30 m
ZK4800-8022-0035	3.50 m
ZK4800-8022-0038	3.80 m
ZK4800-8022-0039	3.90 m
ZK4800-8022-0040	4.00 m
ZK4800-8022-0042	4.20 m
ZK4800-8022-0043	4.30 m
ZK4800-8022-0044	4.40 m
ZK4800-8022-0045	4.50 m
ZK4800-8022-0046	4.60 m
ZK4800-8022-0048	4.80 m
ZK4800-8022-0049	4.90 m
ZK4800-8022-0050	5.00 m
ZK4800-8022-0053	5.30 m
ZK4800-8022-0054	5.40 m
ZK4800-8022-0055	5.50 m
ZK4800-8022-0057	5.70 m
ZK4800-8022-0060	6.00 m

ZK4800-8022-0062	6.20 m
ZK4800-8022-0064	6.40 m
ZK4800-8022-0065	6.50 m
ZK4800-8022-0067	6.70 m
ZK4800-8022-0070	7.00 m
ZK4800-8022-0072	7.20 m
ZK4800-8022-0075	7.50 m
ZK4800-8022-0077	7.70 m
ZK4800-8022-0080	8.00 m
ZK4800-8022-0081	8.10 m
ZK4800-8022-0083	8.30 m
ZK4800-8022-0085	8.50 m
ZK4800-8022-0087	8.70 m
ZK4800-8022-0090	9.00 m
ZK4800-8022-0091	9.10 m
ZK4800-8022-0094	9.40 m
ZK4800-8022-0095	9.50 m
ZK4800-8022-0100	10.00 m
ZK4800-8022-0101	10.10 m
ZK4800-8022-0105	10.50 m
ZK4800-8022-0110	11.00 m
ZK4800-8022-0115	11.50 m
ZK4800-8022-0120	12.00 m
ZK4800-8022-0130	13.00 m
ZK4800-8022-0135	13.50 m
ZK4800-8022-0140	14.00 m
ZK4800-8022-0150	15.00 m
ZK4800-8022-0160	16.00 m
ZK4800-8022-0170	17.00 m
ZK4800-8022-0180	18.00 m
ZK4800-8022-0190	19.00 m
ZK4800-8022-0200	20.00 m
ZK4800-8022-0210	21.00 m
ZK4800-8022-0220	22.00 m
ZK4800-8022-0230	23.00 m
ZK4800-8022-0240	24.00 m
ZK4800-8022-0250	25.00 m

ZK4800-8022-0260	26.00 m
ZK4800-8022-0270	27.00 m
ZK4800-8022-0280	28.00 m
ZK4800-8022-0290	29.00 m
ZK4800-8022-0300	30.00 m
ZK4800-8022-0310	31.00 m
ZK4800-8022-0320	32.00 m
ZK4800-8022-0330	33.00 m
ZK4800-8022-0340	34.00 m
ZK4800-8022-0350	35.00 m
ZK4800-8022-0360	36.00 m
ZK4800-8022-0370	37.00 m
ZK4800-8022-0380	38.00 m
ZK4800-8022-0390	39.00 m
ZK4800-8022-0400	40.00 m
ZK4800-8022-0420	42.00 m
ZK4800-8022-0430	43.00 m
ZK4800-8022-0440	44.00 m
ZK4800-8022-0450	45.00 m
ZK4800-8022-0480	48.00 m
ZK4800-8022-0500	50.00 m

Beckhoff®, ATRO®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, MX-System®, Safety over EtherCAT®, TC/BSD®, TwinCAT®, TwinCAT/BSD®, TwinSAFE®, XFC®, XPlanar® and XTS® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2026

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.